



SAFETY DATA SHEET SAFECLENE 200 ML

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name SAFECLENE 200 ML
Product No. SCL, ASCL200, ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Office Equipment Cleaning Product
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier AF INTERNATIONAL. A division of HK
WENTWORTH LTD
ASHBY PARK
COALFIELD WAY
ASHBY de la ZOUCH
LEICESTERSHIRE. LE65 1JR
UNITED KINGDOM
+44 (0) 1530 419600
+44 (0) 1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Xn;R20/21/22, R68/20/21/22. R52/53.

2.2. Label elements

Contains METHANOL

Labelling



Harmful

Risk Phrases

R20/21/22	Harmful by inhalation, in contact with skin and if swallowed.
R68/20/21/22	Harmful: possible risk of irreversible effects through inhalation, in contact with skin and if swallowed.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety Phrases

A1	Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children.
S23	Do not breathe vapour/spray.
S16	Keep away from sources of ignition - No smoking.
S36/37	Wear suitable protective clothing and gloves.

SAFECLENE 200 ML

S51

Use only in well-ventilated areas.

2.3. Other hazards**SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS****3.2. Mixtures**

A MIXTURE OF: (R,R)-1,1,1,2,2,3,4,5,5,5-DECAFLUOROPENTANE, (S,S)-1,1,1,2,2,3,4,5,5,5-DECAFLUOROPENTANE		60-80%
CAS-No.: -	EC No.: 420-640-8	
Classification (EC 1272/2008) Aquatic Chronic 3 - H412	Classification (67/548/EEC) R52/53	
METHANOL		1-5%
CAS-No.: 67-56-1	EC No.: 200-659-6	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Acute Tox. 3 - H301 Acute Tox. 3 - H311 Acute Tox. 3 - H331 STOT SE 1 - H370	Classification (67/548/EEC) F;R11 T;R23/24/25,R39/23/24/25	
DIMETHYL ETHER		1-5%
CAS-No.: 115-10-6	EC No.: 204-065-8	
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures****Inhalation**

Move the exposed person to fresh air at once. Get medical attention. Provide rest, warmth and fresh air.

Ingestion

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Remove victim immediately from source of exposure. Get medical attention immediately! Provide rest, warmth and fresh air.

Skin contact

Wash the skin immediately with soap and water. Get medical attention promptly if symptoms occur after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptomatically

SECTION 5: FIREFIGHTING MEASURES**5.1. Extinguishing media**

SAFECLENE 200 ML**Extinguishing media**

Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture**Hazardous combustion products**

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Unusual Fire & Explosion Hazards

Aerosol cans may explode in a fire.

Specific hazards

Aerosol containers can explode when heated, due to excessive pressure build-up.

5.3. Advice for firefighters**Special Fire Fighting Procedures**

Containers close to fire should be removed immediately or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES**6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers. Do not contaminate water sources or sewer.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. The product contains a substance which is hazardous to aquatic organisms and which may cause long term adverse effects in the aquatic environment. See section 12 as well. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE**7.1. Precautions for safe handling**

Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**8.1. Control parameters**

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
DIMETHYL ETHER	WEL	400 ppm	766 mg/m ³	500 ppm	958 mg/m ³	
METHANOL	WEL	200 ppm	266 mg/m ³	250 ppm	333 mg/m ³	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

8.2. Exposure controls**Protective equipment**

SAFECLENE 200 ML**Process conditions**

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. It is recommended to use respiratory equipment with combination filter, type A2/P3. EN14387

Hand protection

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Gloves of nitrile rubber, PVA or Viton are recommended. Gloves should conform to EN374

Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable. If risk of splashing, wear safety goggles or face shield. EN166

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Wash promptly with soap & water if skin becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Colourless.
Solubility	Immiscible with water
Initial boiling point and boiling range	>55
Relative density	1.37 - 1.40 @ 20 °c

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not available.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid contact with acids and oxidising substances.

10.5. Incompatible materials**Materials To Avoid**

Strong acids. Strong alkalis. Strong oxidising substances.

10.6. Hazardous decomposition products

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

SAFECLENE 200 ML

11.1. Information on toxicological effects

Inhalation

Harmful by inhalation. May cause irritation to the respiratory system.

Ingestion

Harmful if swallowed.

Skin contact

Harmful in contact with skin. Irritating to skin.

Eye contact

Irritating to eyes.

Health Warnings

Intentional misuse by concentrating / inhaling contents may be lethal

Target Organs

Skin Eyes Respiratory system, lungs

Toxicological information on ingredients.

METHANOL (CAS: 67-56-1)

Toxic Dose 1 - LD 50

9100 mg/kg (oral rat)

Toxic Conc. - LC 50

145000 ppm/4h (inh-rat)

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

No negative effects on the aquatic environment are known.

12.1. Toxicity

Ecological information on ingredients.

METHANOL (CAS: 67-56-1)

LC 50, 96 Hrs, Fish mg/l

10800

EC 50, 48 Hrs, Daphnia, mg/l

24500

IC 50, 72 Hrs, Algae, mg/l

8000

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

Ecological information on ingredients.

METHANOL (CAS: 67-56-1)

Bioaccumulative potential

The product is not bioaccumulating.

12.4. Mobility in soil

SAFECLENE 200 MLEcological information on ingredients.METHANOL (CAS: 67-56-1)**Mobility:**

The product is soluble in water.

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS**13.1. Waste treatment methods**

Dispose of waste and residues in accordance with local authority requirements. Empty containers must not be burned because of explosion hazard.

SECTION 14: TRANSPORT INFORMATION**14.1. UN number**

UN No. (ADR/RID/ADN)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950

14.2. UN proper shipping name

Proper Shipping Name	AEROSOLS
----------------------	----------

14.3. Transport hazard class(es)

ADR/RID/ADN Class	2
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.2
IMDG Class	2.2
ICAO Class/Division	2.2

Transport Labels**14.4. Packing group**

ADR/RID/ADN Packing group	N/A
IMDG Packing group	N/A
ICAO Packing group	N/A

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

EMS	F-D, S-U
Tunnel Restriction Code	(E)

SAFECLENE 200 ML**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

No information required.

SECTION 15: REGULATORY INFORMATION**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Uk Regulatory References**

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.
Chemicals (Hazard Information & Packaging) Regulations.

Environmental Listing

Control of Pollution Act 1974. Control of Pollution (Special Waste Regulations) Act 1980. Rivers (Prevention of Pollution) Act 1961.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment**SECTION 16: OTHER INFORMATION****Revision Comments**

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

Issued By Helen O'Reilly

Revision Date JULY 2010

Revision 5

SDS No. 10418

Risk Phrases In Full

R12	Extremely flammable.
R20/21/22	Harmful by inhalation, in contact with skin and if swallowed.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R68/20/21/22	Harmful: possible risk of irreversible effects through inhalation, in contact with skin and if swallowed.
R11	Highly flammable
R23/24/25	Toxic by inhalation, in contact with skin and if swallowed.
R39/23/24/25	Toxic: danger of very serious irreversible effects through inhalation, in contact with skin and if swallowed.

SAFECLENE 200 ML

Hazard Statements In Full

H220	Extremely flammable gas.
H225	Highly flammable liquid and vapour.
H301	Toxic if swallowed.
H302	Harmful if swallowed.
H311	Toxic in contact with skin.
H312	Harmful in contact with skin.
H331	Toxic if inhaled.
H332	Harmful if inhaled.
H370	Causes damage to organs <<Organs>>.
H371	May cause damage to organs <<Organs>>.
H412	Harmful to aquatic life with long lasting effects.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.