



HP-2002AC

200Mbps PowerLine Ethernet Adapter with integrated power socket



USES THE EXISTING POWER LINE TO BUILD UP THE NETWORK

The HP-2002AC turns the existing electrical wires in your home or office into a high-speed network. You do not have to install the network cables and be annoyed with the cables planning. Just use the electrical wires that already run through the building to turn it into a data network!

INTEGRATES ELECTRICAL OUTLET AND MAIN FILTER

The HP-2002AC built in an electrical outlet and main filter. The integrated power outlet ensures no electrical outlet is lost when using the HP-2002AC. The integrated main filter gives a predictable and dependable data transmission speed. You won't experience a sudden speed drop when a high power consuming electrical device is been using.

SUPPORTS IGMP & 200MBPS HOMEPLUG AV STANDARD

The HP-2002AC not only complies with the HomePlug AV standard but also supports IGMP managed multicast session. HomePlug AV represents the next generation technology which providing high speed data rate, up to 200Mbps with the coverage up to 300 meters. IGMP can be used for online streaming video, like IPTV, online gaming, DVR and set-top box. IGMP allows more efficient use of resources. With IGMP multicast, the HP-2002AC can save the bandwidth of powerline. You are able to transfer high-definition video and digital audio by simply connecting the device to an electrical outlet via the HP-2002AC.

COEXISTENCE WITH HOMEPLUG 1.0 & 1.0 TURBO

The HP-2002AC is designed to ensure the efficient coexistence with the HomePlug 1.0 and 1.0 Turbo devices . You can use HP-2002AC and other HomePlug 1.0 stations to build up one network. You don't have to worry the interoperability issue.

SUPPORTS QoS & 128-bits AES ENCRYPTION

The HP-2002AC not only provides Quality of Service (QoS), including guaranteed bandwidth reservation, high reliability and tight control of latency, but also supports 128-bits AES link encryption for security. It is a good choice for you to create a new network or to rearrange the existing network.

SUPPORTS GROUP BUTTON & RESET BUTTON

The HP-2002AC provides hardware "Group Button" and "Reset Button" for you to simplify the configuration. The "Group Button" can help you to setup network password of powerline automatically. Press the "Reset Button" for 3 seconds to reset the configuration to factory default.

FEATURES AND TECHNICAL SPECIFICATIONS

HARDWARE INTERFACE	MODULATION	POWER
<ul style="list-style-type: none"> 1 Power jack + 1 LAN 10/100Mbps Ethernet Port LED Indicators: Power, Ethernet and Powerline Reset button Group button 	<ul style="list-style-type: none"> 1024/256/64/16-QAM, QPSK, BPSK and ROBO Modulation Schemes 	<ul style="list-style-type: none"> 100~240VAC , 50~60Hz
SECURITY & SUPPORT OS	FREQUENCY BAND & HARDWARE	HUMIDITY
<ul style="list-style-type: none"> 128-bit AES link Encryption Support Windows 98SE/ME/2000/32&64 bit XP/32&64 bit Vista 	<ul style="list-style-type: none"> 2~30 MHz 128Mbits SDRAM 16Mbits Flash 	<ul style="list-style-type: none"> 10-90% (Non-condensing)
FUNCTIONS	DIMENSION & TEMPERATURE	CERTIFICATIONS
<ul style="list-style-type: none"> Powerline Coverage Range up to 300 meters Supports IPv6 IGMP managed multicast IP transmission Integrated Quality of Service (QoS) : Support contention-free access, four-level priority contention access, and multi segment bursting Support VLAN Priority, ToS and CoS Packet Classifier 	<ul style="list-style-type: none"> 134 x 68 x 45 mm 0~45 Degree Celsius 	<ul style="list-style-type: none"> CE

NETWORK SETUP DIAGRAM AND RELATED PRODUCTS

An example of how the HP-2002AC can be setup :

- Plug the HP-2002AC to the power outlet and connect to Broadband router.
- Plug the other HP-2002AC to the power outlet and connect to computer's Ethernet port .

