


# Mains Flex - 3 Core Cable

## Coiled (0.2, 0.75 and 1.25mm<sup>2</sup>)

pro-POWER



### Specifications:

#### 3 core 0.75mm<sup>2</sup> spiral cable

Cores Quantity	: 3
Core Size	: 0.75mm <sup>2</sup>
Construction	: 24/0.2 plain copper
Cores Insulation	: PVC
Cable	: BS 6500
Sheath Material	: PVC
Sheath Colour	: Black or white
Sheath Outer Diameter	: 6.8mm
Inside Diameter	: 9.5mm
Coil Outer Diameter	: 24mm
Closed Coil Length	: 500mm
Tails (Tangent)	: 150mm
Extended Length	: 2,500mm
Voltage	: 300V/500V
Current	: 6A

#### 3 core 1mm<sup>2</sup> spiral cable

Cores Quantity	: 3
Core Size	: 1mm <sup>2</sup>
Construction	: 32/0.2 plain copper


#### 3 core 1mm<sup>2</sup> spiral cable:

Cores Insulation	: PVC
Cable	: BS 6500
Sheath Material	: PVC
Sheath Colour	: Black or White
Sheath Outer Diameter	: 7.2mm
Inside Diameter	: 9.5mm
Coil Outer Diameter	: 25mm
Closed Coil Length	: 500mm
Tails (Tangent)	: 150mm
Extended Length	: 2,500mm
Voltage	: 300V/500V
Current	: 10A

# Mains Flex - 3 Core Cable

## Coiled (0.2, 0.75 and 1.25mm<sup>2</sup>)

pro-POWER



Specifications Table:

Item	A	B	C	D	Cable Marking	Basic Cable	Outer Dia. (mm)	Length (m)	
	Coils	Tails (mm)	Overall Dia. (mm)	Inside Dia. (mm)					
15/X/11 BLACK 1A	25 ±2 (approx. 12.19 to 143.1mm)	150 ±10mm	20.6 ±3	10 ±2	-	18/0.12mm BC × 3C (Blue, Brown, Yellow/Green) + PVC Insulated + PVC Sheath	5.3	1.5	
15/X/10 BLACK 6A					-				
10A MAINS BLK					-				
15/X/9 BLACK 13A	36 ±2 (approx. 281.18 to 314.26mm)		26.5 ±3		SAMSON BS6500 H05VV-F 3 × 1.25	110/0.12mm BC × 3C (Blue, Brown, Yellow/Green) + PVC Insulated + PVC Sheath	8.27	2.36	
15/X/11 WHITE 1A	25 ±2 (approx. 12.19 to 143.1mm)		20.6 ±3		-	18/0.12mm BC × 3C (Blue, Brown, Yellow/Green) + PVC Insulated + PVC Sheath	5.3	1.5	
15/X/10 WHITE 6A									-
10A MAINS WHT									-
15/X/9 WHITE 13A	36 ±2 (approx. 281.18 to 314.26mm)		26.5 ±3		SAMSON BS6500 H05VV-F 3 × 1.25	110/0.12mm BC × 3C (Blue, Brown, Yellow/Green) + PVC Insulated + PVC Sheath	8.27	2.36	
10A MAINS GREY									

# Mains Flex - 3 Core Cable

## Coiled (0.2, 0.75 and 1.25mm<sup>2</sup>)

pro-POWER

### Nominal Dimensions:

Core Colour	Size mm <sup>2</sup>	Contact Number	Function
Blue	0.75	-	-
Brown		-	-
Green/Yellow		-	-
Blue	1	-	-
Brown		-	-
Green/Yellow		-	-

### Part Number Table:

Description	Part Number
Cable, Mains, Coiled, 0.75mm	15/X/10 BLACK 6A
Cable, Mains, Coiled, 1mm	10A MAINS BLK
Cable, Mains, Coiled, 0.75mm	15/X/10 WHITE 6A
Cable, Mains, Coiled, 1mm	10A MAINS WHT
Cable, Mains, Coiled, 1mm	10A MAINS GREY
Cable, Mains, Coiled, 0.22mm	15/X/11 BLACK 1A
Cable, Mains, Coiled, 1.25mm	15/X/9 BLACK 13A
Cable, Mains, Coiled, 0.22mm	15/X/11 WHITE 1A
Cable, Mains, Coiled, 1.25mm	15/X/9 WHITE 13A

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)  
[www.cpc.co.uk](http://www.cpc.co.uk)

pro-POWER