




Features:

- Conform to EN 60309-1 and -2 standards
- Body, inserts and locknut made of insulating, thermoplastic, self-extinguishing material
- PE...SV (IP44) types, entry with cable gland in operating voltage colour, RAL 7035 grey colour body
- Fixing captive screws
- IP44 degree of protection (EN 60529)



Dimensions

Poles	Frequency Hz	Voltage V	A	8	Ø Min.	Ø Max.
12 P +	50 and 60	200 ÷ 250	129	59.5	7	16
3 P +		380 ÷ 415		67		
3 P + N +		200 / 346 ÷ 240 / 415		75	8	24

Dimensions : Millimetres

Part Number Table

Description	No. of Positions	Part Number
Plug, 16A, 110V, IP44	2P + E	PE1643SV
Plug, 16A, 240V, IP44	2P + E	PE1663SV
Plug, 16A, 415V, IP44	3P + E	PE1664SV
Plug, 16A, 415V, IP44	3P + N + E	PE1665SV

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.