


DASH NO.	M CODE	MADE FROM
----------	--------	-----------

SD



STAMP: KINGS 2065-1-9
YR WK (DATE CODE)

NOTES:

- FOR USE WITH BELDEN 9209 & 8279 CABLES.
- FOR CABLING INSTRUCTIONS SEE 3-661-1.
- FOR CRIMPING USE DIE KTH-2261.
- INTERFACE PER MIL-STD-348, FIG 301.1, AS APPLICABLE.
- MATERIALS:
 INSULATOR-TEFLON, ASTM-D-4894
 GASKET-SILICONE RUBBER, ZZ-R-765
 SPRING WASHER }
 OUTER CONTACT } BER. COP., ASTM-B-196
 K-GRIP SLEEVE-COMMERCIAL BRONZE, ASTM-B-135
 ALL OTHER METAL PARTS-BRASS, ASTM-B16
- FINISHES:
 CENTER CONTACTS-GOLD PLATE PER MIL-G-45204
 SPRING WASHER-SILVER PLATE PER QQ-S-365
 ALL OTHER METAL PARTS-KINGS TARNISH RESISTANT NICKEL FINISH (TR-5)
- ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE-75 OHMS
 WORKING VOLTAGE-500 VRMS
 FREQUENCY RANGE-DC TO 3 GHZ

2065-1-9

REVISIONS

ISSUE	CHANGES
0	ER 37764 DCT 01/08/99
1	CN 37782 E DCT 01/29/99
2	CN 37804 E TML 04/01/99
3	CN 37836 C TML 05/20/99
4	CN 37932 D TML 11/08/99
5	CN 38011 D HVN 05/23/00
6	CN 38495 E TML 02/01/02

206519S

SCALE	4:1		
APPROX SURFACE AREA			
USED ON			
REF:			
PL, 75 BNC			
DRAWN	TML	DATE	01/08/99
DESIGN	DCT	DATE	01/08/98
APPR.		DATE	

KINGS
ELECTRONICS CO., INC.
ROCK HILL, SOUTH CAROLINA 29730

2065-1-9

SD

UNLESS OTHERWISE SPECIFIED	2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.	7. ALL LEAD THREADS TO BE CHAMFERED 45° TO ROOT DIAMETER. * CRITICAL DIMENSIONS
1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010	3. NO FILLETS PERMITTED.	
3 PLACE DECIMALS ± .004 ANGLES ± 1°	4. SURFACE ROUGHNESS 63 MICRONS RMS MAX.	
CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.	5. ALL DIMENSIONS PRIOR TO PLATING.	
	6. ALL PLATING IN ACCORDANCE WITH KER 10004.	