



## Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 4

Loctite 7855

sds no. : 173179

V002.4

Revision: 25.01.2012

printing date: 18.06.2013

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

**Product identifier:**

Loctite 7855

**Relevant identified uses of the substance or mixture and uses advised against:**

Intended use:  
Handcleaner

**Details of the supplier of the safety data sheet:**

Henkel Limited  
Apollo Court, 2 Bishop Square Business Park  
AL10 9EY Hatfield

Great Britain

Phone: +44 (1707) 635000

Fax-no.: +44 (1707) 635099

ua-productsafety.uk@uk.henkel.com

**Emergency Telephone Number:**

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

**Classification of the substance or mixture:**

**Label elements (DPD):**

Risk phrases:  
not applicable

**Other hazards:**

This Information Sheet has been prepared in accordance with the requirements of EC Directive 76/768/EEC and other related directives, on the approximation of the laws of the member states relating to cosmetic products.

### SECTION 3: Composition/information on ingredients

**Declaration of ingredients according to DPD (EC) No 1999/45:**

This Information Sheet has been prepared in accordance with the requirements of EC Directive 76/768/EEC and other related directives, on the approximation of the laws of the member states relating to cosmetic products.

### SECTION 4: First aid measures

**Description of first aid measures:**

**Inhalation:**

Should not be a problem as product is of low volatility. However, if feeling unwell remove patient to fresh air.

Skin contact:  
Wash skin with water

Eye contact:  
Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:  
Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.  
Seek medical advice.

### SECTION 5: Firefighting measures

**Combustion behaviour:**  
Non-combustible.

### SECTION 6: Accidental release measures

**Methods and material for containment and cleaning up:**  
For small spills wipe up with paper towel and place in container for disposal.  
For large spills absorb onto inert absorbent material and place in sealed container for disposal.

### SECTION 7: Handling and storage

**Precautions for safe handling:**  
No particular measures required.

Hygiene measures:  
No particular measures required.

**Conditions for safe storage, including any incompatibilities:**  
Store in a cool, well-ventilated place.

**Specific end use(s):**  
Handcleaner

### SECTION 8: Exposure controls/personal protection

**Control parameters:**  
Valid for  
Great Britain

None

**Exposure controls:**

Hand protection:  
Not needed.

**SECTION 9: Physical and chemical properties****Information on basic physical and chemical properties:**

Appearance	emulsion greyish
Odor	Pleasant
Appearance	emulsion greyish
Odor	Pleasant
pH	5 - 8
( )	
Initial boiling point	No data available / Not applicable
Flash point	88 - 92 °C (190.4 - 197.6 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	1,06 - 1,09 g/cm <sup>3</sup>
( )	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Miscible
(Solvent: Water)	
Solubility (qualitative)	Miscible
(Solvent: Acetone)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**Other information:**

No data available / Not applicable

**SECTION 10: Stability and reactivity****Possibility of hazardous reactions:**

See section reactivity

**Conditions to avoid:**

Stable under normal conditions of storage and use.

**SECTION 11: Toxicological information****Oral toxicity:**

This material is considered to have low toxicity if swallowed.

**Inhalative toxicity:**

Due to the low volatility of the product there are no hazards associated with inhalation under normal conditions of use

**Dermal toxicity:**

This product is considered to have low dermal toxicity.  
It is intended for use as a hand cleaner

**Eye irritation:**

May cause mild irritation to the eyes.

## SECTION 12: Ecological information

### General ecological information:

Biodegradable product of low ecotoxicity.

## SECTION 13: Disposal considerations

### Waste treatment methods:

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Disposal must be made according to official regulations.

## SECTION 14: Transport information

### Road transport ADR:

Not dangerous goods

### Railroad transport RID:

Not dangerous goods

### Inland water transport ADN:

Not dangerous goods

### Marine transport IMDG:

Not dangerous goods

### Air transport IATA:

Not dangerous goods

## SECTION 15: Regulatory information

### Safety, health and environmental regulations/legislation specific for the substance or mixture:

VOC content < 3 %  
(1999/13/EC)

## SECTION 16: Other information

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This Information Sheet has been prepared in accordance with the requirements of EC Directive 76/768/EEC and other related directives, on the approximation of the laws of the member states relating to cosmetic products.