Standard Female Connectors picoMAX[®] 5.0

Gripping plate dimensions (in mm):

В

1.5

1.5

1.5

1.5

1.5

6.5

1.5

6.5

с

-

3.5

3.5

3.5

5.0

5.0

D

20

20

20

25

25

25

35

35

Е

_

9

9

9

19

19

Α

7

12

12

22

22

22

42

42

Pole No.

2

3

4

5

6

8

10


12



29



Push down sliding connector release (gripping plate) to open the locking latch.




Pull out female connector with gripping plate from male header.

WAGO








Standard Female Connectors picoMAX[®] 5.0

28




- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Ability to wire while mated or unmated
- Testing port parallel to conductor entry tip contact
- Integrated locking latches prevent accidental disconnection

Technical data:

Pin Spacing	5 mm 0.197 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	111	Ш
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Approvals per	UL/CSA*		
Use group UL 1059	В	С	D
Rated voltage	300 V	-	300 V
Nominal current UL	15 A	-	10 A
Nominal current CSA	-	-	-

Conductor data:

Connection technology	CAGE CLAMP [®] S
Conductor size: solid	0.2 - 2.5 mm ²
Conductor size: fine-stranded	0.2 - 2.5 mm ²
Conductor size: fine-stranded	0.25 - 1.5 mm ² (with insulated ferrule)
Conductor size: fine-stranded	0.25 – 2.5 mm ² (with uninsulated ferrule)
AWG	24 – 12 12: THHN, THWN
Strip length	9 - 10 mm / 0.35 - 0.39 in



For additional derating curves, see page 72.

Page:

64

68

65

66

64

Accessories for picoMAX®:

Material data:

Material group	- I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	VO
Lower/Upper limit temperature	-60 °C / +100 °C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E _{c.})
Contact plating	tin-plated

The **picoMAX®** pluggable connection system includes connectors without breaking capacity in accordance with DIN (EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

Operating tools

Gripping plates

Coding pins

Test pin


Direct printing

Number: 2134310.01		1.1	EMA
lanued to			EMA
Applicant		IN	EUR
	_		
Wego-Kontaktischnik Gmbi Hanaastrasse 27 32423. Minden/westfalen, G			
Manufacturent inernee	erenter (
Wasulacturent, censee Waso-Kontakttechnik Gebi	н		
Hansastrasse 27			
32423, Minden/westfaleri, G	emery		
Productin) applar	ca connectory		
Trade name(s) WAGO			
Type(s)/model(k) 2091			
The product and any acceptal therein referred to.	ble variation therefo is specified in the A	mex to this certificate and the do	cuments
	Charles and the second second	and the state of the state of the	
KEMA Quality hereby declara	is that the above-mentioned product has	been certified on the basis of	
 a type test according to it 	e standard EN 61984 2008; action location according to CENELEC 0	Summing of Party many Call (22)	
 a certification agreement 		And a second second second second second	
KEMA Quality hereby grants t	the right to use the KEMA-KEUR certific	ation mark.	
The VENA VEL D confliction	mark may be applied to the product as	sourcement in the continues for the	denter of the
KEMA-KEUR ownification age	wement and under the conditions of the	KEMA-KEUR Aertification agreen	rent.
This certificate is issued on A	April 2010 and expires upon withdraws	of one of the above mentioned	dandards.
KEMA Quality B.V.			
a s			
Rod	>=		
g	>=		
Real and	F.S. Spikwerds		
The C.I. Zostowe	E.S. Spriverois Centration Manager	ACCREDITED BY	0
Rest	Certification Manager	ACCREDITED BY THE DUTCH COLINCIL FOR ACCREDITATION	Q


Handling *picoMAX*[®] Pin Spacing: 3.5 mm/0.138 in; 5.0 mm/0.197 in; 7.5 mm/0.295 in



Inserting fine-stranded conductor into unmated female connector via push-button.



Inserting fine-stranded conductor into mated female connector via push-button.




Inserting solid and ferruled conductors via push-in termination (see notes on page 75).




Easy-to-identify PCB inputs and outputs.



"Wire-to-wire" flying leads





Male connectors with snap-in mounting feet for panel mounting.

solid



CAGE CLAMP® S clamps the following copper conductors:



Male connector with snap-in mounting feet on mounting adapter for DIN 35 rail.





Pole marking via factory direct printing.




fine-stranded, also with tinned single strands







Male header mated to a female connector with gripping plate and sliding connector release.



- Disconnecting female connector via sliding connector release.
 Push down sliding connector release (gripping plate) to open the locking latch.
 Pull out female connector from male header.




Disconnecting female connector via unlocking tool. Plug unlocking tool into the male locking latch.





Insert unlocking tool until it hits backstop. Wedge opens locking latches.



Pull on both unlocking tool and conductors to remove female connector from male header.



Coding a female connector (via coding key carrier and two keys for female connector, see symbol).



Coding a male header (via coding key carrier and two keys for male header, see symbol). Unlocking tool may be suspended on wire harness for storage.





fine-stranded, tip-bonded



fine-stranded, with ferrule (gastight crimped)

