

# 3M™ LED advanced light BR-30



## Features:

- 12 watts replaces 75W incandescent lamps
- Dimmable to 5% with most incandescent dimmers
- 50,000-hour life, 5-year warranty
- No UV or IR radiation
- 0.9 power factor
- Voltage: 120 VAC
- Socket Type: medium screw base
- Environment: dry locations
- Length: 5.25 in, 134 mm
- Diameter: 3.75 in, 95 mm
- Weight: 12.5 oz, 354 g

The 3M™ LED advanced light BR-30 is an energy-efficient downlight designed to last 50,000 hours. These dimmable bulbs require just 12 watts to match the lumens in traditional 75W incandescent bulbs. Their smooth beam patterns and warm, white light are ideal for general illumination in a wide range of residential and hospitality applications.




Catalog #	Lumens	CCT (deg K)	Power (W)	Beam Angle	CRI
<b>RCBR30B27</b>	810	2700	12	Flood	82
<b>RCBR30B3</b>	830	3000	12	Flood	82




# 3M™ LED advanced light BR-30


Candela Distribution



Beam Distribution



0° Aiming Footcandles



## Ordering Information

Catalog #	Description	Stock Number	Billing Unif	Case Qty.	MOQ	Item UPC	Case UPC	Case Dimension (L x W x H)	Case Weight (lbs.)	Case Cube (cu. ft.)
RCBR30B27	BR-30 2700K, Flood, Dimmable	70-0800-3007-8	EA	16	1 case	000-51128-94397-7	500-51128-94397-2	17.1" x 8.6" x 10.5"	10	0.894
RCBR30B3	BR-30 3000K, Flood, Dimmable	70-0800-3008-6	EA	16	1 case	000-51128-94398-4	500-51128-94398-9	17.1" x 8.6" x 10.5"	10	0.894

Halogen Free is defined as having less than 900 ppm bromine, less than 900 ppm chlorine, and less than 1500 ppm total bromine and chlorine; other halogens are excluded from this definition. These are levels set forth in certain industry standards, such as International Electrotechnical Commission (IEC) 61249-2-21 standard. This information is 3M's current knowledge and belief, which may be based in whole or in part on information provided by its suppliers.

3M is a trademark of 3M Company. All other trademarks herein are the property of their respective owners.

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

## Warranty; Limited Remedy; Limited Liability.

Warranted to last 5 years based on 12 hours normal use per day at 120 volts. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



## Electrical Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000  
800 245 3573  
FAX 800 245 0329  
www.3M.com/led

Please recycle. Printed in USA.  
© 3M 2013. All rights reserved.  
80-6016-0718-9