# Type MLP 85 °C Flatpack, Ultra Long Life, Aluminum Electrolytic

## Very Low Profile



The MLP's high-energy storage and box-shape make it perfect for voltage holdup or filtering in military SEM-E modules, telecom circuit packs and computer cards. The MLP delivers up to 20 joules of energy storage in a 1/2" height with 50 year's life at +45 °C. You can readily heatsink it to double the ripple-current capability. The MLP is the square-peg component that fits the square-holes in electronic assemblies.

## Highlights

- Low-profile replacement for snap-ins
- Double the ripple capability with a heatsink
- Nearly hermetic welded seal assures 50-year life
- Withstands more than 80,000 feet altitude

| Temperature Range               | -55°C to +85°C ≤250 Vdc   |  |  |  |  |  |  |  |
|---------------------------------|---|--|--|--|--|--|--|--|
|                                 | -40°C to +85°C ≥300 Vdc   |  |  |  |  |  |  |  |
| Rated Voltage Range             | 7.5 Vdc to 450 Vdc  |  |  |  |  |  |  |  |
| Capacitance Range               | 110 μF to 47,000 μF   |  |  |  |  |  |  |  |
| Capacitance Tolerance           | ±20%  |  |  |  |  |  |  |  |
| Leakage Current                 | $\leq$ 0.002 CV µA, @ 25 °C and 5 min.  |  |  |  |  |  |  |  |
| Ripple Current Multipliers      | Ambient Temperature, No Heatsink  |  |  |  |  |  |  |  |
|                                 | 45 ℃ 55 ℃ 65 ℃ 75 ℃ 85 ℃  |  |  |  |  |  |  |  |
|                                 | 1.00 0.90 0.75 0.56 0.27  |  |  |  |  |  |  |  |
|                                 | Case Temperature  |  |  |  |  |  |  |  |
|                                 | <b>45 ℃ 55 ℃ 65 ℃ 75 ℃ 85 ℃</b>   |  |  |  |  |  |  |  |
|                                 | 3.79 3.32 2.77 2.08 1.00  |  |  |  |  |  |  |  |
|                                 | Frequency   |  |  |  |  |  |  |  |
|                                 | 50 Hz 60 Hz 120 Hz 360 Hz 1 kHz 5 kHz & up  |  |  |  |  |  |  |  |
|                                 | 7.5 to 63 V         0.94         0.95         1.00         1.04         1.05         1.06         1.06           80 to 450 V         0.80         0.85         1.00         1.17         1.24         1.28         1.29 |  |  |  |  |  |  |  |
| Low Temperature Characteristics | Impedance ratio: $Z_{-55^{\circ}C} / Z_{+25^{\circ}C}$ $\leq 10$ (7.5 - 20 Vdc) $\leq 2$ (25 - 250 Vdc)         Impedance ratio: $Z_{-20^{\circ}C} / Z_{+25^{\circ}C}$ $\leq 4$ (300-450Vdc)                            |  |  |  |  |  |  |  |
| Endurance Life Test             | 2000 h @ full load at +85 °C<br>$\Delta$ Capacitance ±10%<br>ESR 200% of limit<br>DCL 100% of limit   |  |  |  |  |  |  |  |
| Shelf Life Test                 | 500 h at 85 °C<br>Capacitance 100% of limit<br>ESR 100% of limit<br>DCL 100% of limit   |  |  |  |  |  |  |  |
| Vibration                       |   |  |  |  |  |  |  |  |


## **Specifications**

# Type MLP 85 °C Flatpack, Ultra Long Life, Aluminum Electrolytic


## Very Low Profile


| Thermal Resistance        | Large Sides   | Case Length | 1.5" | 2.0" | 3.0" |  |  |  |
|---------------------------|---|-------------|------|------|------|--|--|--|
|                           | Heatsinked  |             | °C/W | °C/W | °C/W |  |  |  |
|                           |   | None        | 3.0  | 1.8  | 1.2  |  |  |  |
|                           | one   | Polyester   | 4.3  | 2.6  | 1.7  |  |  |  |
|                           |   | None        | 2.8  | 1.7  | 1.1  |  |  |  |
|                           | both  | Polyester   | 4.0  | 2.4  | 1.6  |  |  |  |
| ESL                       | <30 nH measured 1/4" from case at 1 MHz   |             |      |      |      |  |  |  |
| Weight                    | Case EK 30 g typical<br>Case EA 42 g typical<br>Case EB 66 g typical  |             |      |      |      |  |  |  |
| Terminals                 | 18 AWG copper wire with 60/40 tin-lead electroplate, 20 amps max  |             |      |      |      |  |  |  |
| Double the Ripple Current | Attach the MLP to an external heatsink and you can easily double the ripple current capability and assure long life through cooler operation. The broad, flat top and bottom on the MLP are ideal for cooling the capacitor and removing the heat caused by ripple current.   |             |      |      |      |  |  |  |
| Ripple Current Capability | The ripple current capability is set by the maximum permissible internal core temperature, 88 °C. This assures that the case does not inflate beyond 0.5 inch height.   |             |      |      |      |  |  |  |
| Air Cooled                | The ripple currents in the ratings tables are for 85 °C case temperatures.<br>For air temperatures without a heatsink use the multipliers Ambient<br>Temperature, No Heatsink.  |             |      |      |      |  |  |  |
| Heatsink Cooled           | Temperature rise from the internal hottest spot, the core, to ambient air is  |             |      |      |      |  |  |  |
|                           | $\Delta T = I^{2}(ESR)(\theta cc + \theta ca)$  |             |      |      |      |  |  |  |
|                           | where $\theta$ cc is the thermal resistance from core to case and $\theta$ ca from case to ambient. To calculate maximum ripple capability with the MLP attached to a heatsink use the maximum core temperature and the values for $\theta$ cc.   |             |      |      |      |  |  |  |
| Example                   | As an illustration, suppose you operate an insulated MLP332M080EB1C in 65 °C air and attach it to a commercial heatsink with a free-air thermal resistance of 2.7 °C/W. Use a good thermal grease between the MLP and the heatsink, and the total thermal resistance is 2.7 +1.7 or 4.4 °C/W. The power which would heat the core to 88 °C is (88-65)/4.4 or 4.75 W. For an ESR of 31 m $\Omega$ , 4.7 W equates to a ripple current of 12.3 A. |             |      |      |      |  |  |  |

## **Part Numbering System**



## **Type MLP 85 °C Flatpack, Ultra Long Life, Aluminum Electrolytic** Very Low Profile Outline Drawings






# Type MLP 85 °C Flatpack, Ultra Long Life, Aluminum Electrolytic

## Very Low Profile


### Ratings

| Cap.<br>(μF)          | Catalog<br>Part Number | ESR max<br>25 °C (mΩ) |            | Ripple (A)<br>Case @ 85 °C |        | Length        | Cap.                    | Catalog                 | ESR max<br>25 °C (mΩ) |           | Ripple (A)<br>Case @ 85 °C |          | Length |  |  |
|-----------------------|------------------------|-----------------------|------------|----------------------------|--------|---------------|-------------------------|-------------------------|-----------------------|-----------|----------------------------|----------|--------|--|--|
|                       |                        | 120 Hz                | 20 kHz     | 120 Hz                     | 20 kHz | (Inches) (µF) | Part Number             | 120 Hz                  | 20 kHz                | 120 Hz    | 20 kHz                     | (Inches) |        |  |  |
|                       | 7.5                    | Vdc (10               | Vdc Surg   | je)                        |        |               | 100 Vdc (125 Vdc Surge) |                         |                       |           |                            |          |        |  |  |
| 19,000                | MLP193M7R5EK0A         | 76                    | 66         | 4.2                        | 4.5    | 1.5           | 1100                    | MLP112M100EK0A          | 112                   | 78        | 3.5                        | 4.2      | 1.5    |  |  |
| 28,000                | MLP283M7R5EA0A         | 50                    | 44         | 5.8                        | 6.2    | 2.0           | 1600                    | MLP162M100EA0A          | 76                    | 54        | 4.7                        | 5.6      | 2.0    |  |  |
| 47,000                | MLP473M7R5EB0A         | 30                    | 26         | 9.1                        | 9.8    | 3.0           | 2700                    | MLP272M100EB0A          | 46                    | 33        | 7.4                        | 8.7      | 3.0    |  |  |
| 10 Vdc (13 Vdc Surge) |                        |                       |            |                            |        |               |                         | 150 Vdc (180 Vdc Surge) |                       |           |                            |          |        |  |  |
| 17000                 | MLP173M010EK0A         | 77                    | 67         | 4.2                        | 4.5    | 1.5           | 500                     | MLP501M150EK0A          | 355                   | 248       | 1.9                        | 2.3      | 1.5    |  |  |
| 26000                 | MLP263M010EA0A         | 51                    | 45         | 5.8                        | 6.1    | 2.0           | 770                     | MLP771M150EA0A          | 238                   | 166       | 2.7                        | 3.2      | 2.0    |  |  |
| 43000                 | MLP433M010EB0A         | 30                    | 27         | 9.0                        | 9.6    | 3.0           | 1300                    | MLP132M150EB0A          | 143                   | 100       | 4.2                        | 5.0      | 3.0    |  |  |
| 16 Vdc (20 Vdc Surge) |                        |                       |            |                            |        |               | 200 Vdc (250 Vdc Surge) |                         |                       |           |                            |          |        |  |  |
| 13000                 | MLP133M016EK0A         | 81                    | 69         | 4.1                        | 4.4    | 1.5           | 400                     | MLP401M200EK0A          | 388                   | 253       | 1.9                        | 2.3      | 1.5    |  |  |
| 21000                 | MLP213M016EA0A         | 53                    | 46         | 5.7                        | 6.1    | 2.0           | 600                     | MLP601M200EA0A          | 261                   | 168       | 2.6                        | 3.2      | 2.0    |  |  |
| 38000                 | MLP383M016EB0A         | 31                    | 27         | 9.0                        | 9.6    | 3.0           | 1000                    | MLP102M200EB0A          | 158                   | 100       | 3.8                        | 5.0      | 3.0    |  |  |
| 20 Vdc (25 Vdc Surge) |                        |                       |            |                            |        |               |                         | 250 Vdc (300 Vdc Surge) |                       |           |                            |          |        |  |  |
| 9600                  | MLP962M020EK0A         | 84                    | 69         | 4.0                        | 4.4    | 1.5           | 330                     | MLP331M250EK0A          | 426                   | 258       | 1.8                        | 2.3      | 1.5    |  |  |
| 14000                 | MLP143M020EA0A         | 56                    | 46         | 5.5                        | 6.1    | 2.0           | 490                     | MLP491M250EA0A          | 285                   | 172       | 2.4                        | 3.1      | 2.0    |  |  |
| 24000                 | MLP243M020EB0A         | 33                    | 27         | 8.7                        | 9.6    | 3.0           | 820                     | MLP821M250EB0A          | 172                   | 103       | 3.8                        | 4.9      | 3.0    |  |  |
| 25 Vdc (30 Vdc Surge) |                        |                       |            |                            |        |               | 300 Vdc (350 Vdc Surge) |                         |                       |           |                            |          |        |  |  |
| 8000                  | MLP802M025EK0A         | 87                    | 69         | 3.9                        | 4.4    | 1.5           | 220                     | MLP221M300EK0A          | 597                   | 393       | 1.5                        | 1.9      | 1.5    |  |  |
| 12000                 | MLP123M025EA0A         | 57                    | 46         | 5.5                        | 6.1    | 2.0           | 330                     | MLP331M300EA0A          | 399                   | 262       | 2.1                        | 2.5      | 2.0    |  |  |
| 20000                 | MLP203M025EB0A         | 34                    | 27         | 8.6                        | 9.6    | 3.0           | 560                     | MLP561M300EB0A          | 240                   | 157       | 3.2                        | 4.0      | 3.0    |  |  |
| 35 Vdc (50 Vdc Surge) |                        |                       |            |                            |        |               |                         | 350 Vdc (400 Vdc Surge) |                       |           |                            |          |        |  |  |
| 5600                  | MLP562M035EK0A         | 90                    | 70         | 3.4                        | 4.4    | 1.5           | 150                     | MLP151M350EK0A          | 1000                  | 734       | 1.2                        | 1.4      | 1.5    |  |  |
| 8400                  | MLP842M035EA0A         | 59                    | 46         | 5.4                        | 6.1    | 2.0           | 220                     | MLP221M350EA0A          | 683                   | 503       | 1.6                        | 1.8      | 2.0    |  |  |
| 14000                 | MLP143M035EB0A         | 35                    | 27         | 8.4                        | 9.6    | 3.0           | 370                     | MLP371M350EB0A          | 420                   | 310       | 2.3                        | 2.8      | 3.0    |  |  |
| 50 Vdc (63 Vdc Surge) |                        |                       |            |                            |        |               |                         | 400                     | Vdc (45               | 0 Vdc Sur | ge)                        |          |        |  |  |
| 4400                  | MLP442M050EK0A         | 97                    | 70         | 3.7                        | 4.4    | 1.5           | 130                     | MLP131M400EK0A          | 1320                  | 970       | 1.0                        | 1.2      | 1.5    |  |  |
| 6600                  | MLP662M050EA0A         | 62                    | 46         | 5.2                        | 6.1    | 2.0           | 200                     | MLP201M400EA0A          | 882                   | 648       | 1.4                        | 1.6      | 2.0    |  |  |
| 11000                 | MLP113M050EB0A         | 36                    | 27         | 8.3                        | 9.6    | 3.0           | 330                     | MLP331M400EB0A          | 530                   | 390       | 2.1                        | 2.5      | 3.0    |  |  |
| 63 Vdc (75 Vdc Surge) |                        |                       |            |                            |        |               | 420 Vdc (475 Vdc Surge) |                         |                       |           |                            |          |        |  |  |
| 2200                  | MLP222M063EK0A         | 101                   | 76         | 3.7                        | 4.2    | 1.5           | 130                     | MLP131M420EK0A          | 1320                  | 970       | 1.0                        | 1.2      | 1.5    |  |  |
| 3300                  | MLP332M063EA0A         | 64                    | 50         | 5.2                        | 5.8    | 2.0           | 200                     | MLP201M420EA0A          | 882                   | 648       | 1.4                        | 1.6      | 2.0    |  |  |
| 5600                  | MLP562M063EB0A         | 36                    | 29         | 8.3                        | 9.3    | 3.0           | 330                     | MLP331M420EB0A          | 530                   | 390       | 2.1                        | 2.5      | 3.0    |  |  |
|                       |                        | /dc (100              | ) Vdc Surg | ge)                        |        |               |                         | 450                     | Vdc (50               | 0 Vdc Sur | ge)                        |          |        |  |  |
| 1500                  | MLP152M080EK0A         | 106                   | 77         | 3.6                        | 4.2    | 1.5           | 110                     | MLP111M450EK0A          | 1456                  | 1190      | 0.96                       | 1.1      | 1.5    |  |  |
| 2100                  | MLP212M080EA0A         | 72                    | 52         | 4.9                        | 5.7    | 2.0           | 170                     | MLP171M450EA0A          | 973                   | 797       | 1.3                        | 1.5      | 2.0    |  |  |
| 3300                  | MLP332M080EB0A         | 44                    | 31         | 7.5                        | 9.0    | 3.0           | 280                     | MLP281M450EB0A          | 585                   | 480       | 2.0                        | 2.3      | 3.0    |  |  |

#### **Typical Performance Curves**




300 V and Up, Operating Life in Kilohours vs Ripple Current




CDM Cornell Dubilier • 140 Technology Place • Liberty, SC 29657 • Phone: (864)843-2277 • Fax: (864)843-3800

## Type MLP 85 °C Flatpack, Ultra Long Life, Aluminum Electrolytic **Very Low Profile**

# **Typical Performance Curves**






1800

1600

2000



Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.