



# Wireless DIN Rail Receiver

## With 4 Analog Outputs and Alarms

UWTC-REC4  
\$275



- ✓ Works with Up to 48 Wireless Transmitters
- ✓ Four 0 to 5 Vdc, 0 to 10 Vdc or 4 to 20 mA Analog Outputs
- ✓ Interface Directly to PLCs, Chart Recorders and Data Loggers
- ✓ Standard DIN Rail Enclosure
- ✓ Built-in Programmable Alarms for Each Channel
- ✓ Field Programmable via USB
- ✓ Included Software Turns a PC Into a Multi-Channel Meter, Chart Recorder or Data Logger

The UWTC-REC4 wireless DIN rail receiver can work with up to 48 wireless transmitters, displaying their data in real time on your PC. The UWTC-REC4 also has four

### Works with:

- UWTC–Thermocouple
- UWRTD–RTD
- UWRH–Humidity
- UWIR–Infrared Temperature
- UWPH–pH
- UWPC–Process Voltage/Current Wireless Transmitters

independent analog outputs, which can be user-programmed as a retransmission signal from any input channel, driving a PLC or data logger. The UWTC-REC4 is compatible with the full line of UW wireless transmitters from OMEGA; choose from thermocouple, RTD, %RH, infrared (non-contact) temperature, pH, as well as process voltage/current models.

The standard DIN rail mount design provides for easy mounting, and fast connections to other DIN rail equipment, including PLCs. The optional iDRN-PS-1000 power supply can power up to three UWTC-REC4 units, which can give you up to 12 analog outputs.

### Specifications

**Power:** 12 to 24 Vdc @ 250 mA

**Analog Output:** 4 independent, non-isolated, retransmission 0 to 5 Vdc, 0 to 10 Vdc or 4 to 20 mA

**Alarms (Programmable):** One per channel, rising/falling activation

**Alarm Type:** Open drain, 100 mA max

**Power, Output, Alarm Connection:** Screw terminals

**Operating Ambient:** 0 to 55°C (32 to 131°F), 90% RH non-condensing

**Radio Frequency (RF) Transceiver Carrier:** ISM 2.4 GHz, direct sequence spread spectrum

**RF Data Packet Standard:** IEEE 802.15.4, open communication architecture

**Enclosure:** DIN rail (plastic)

**Dimensions:** 93 H x 39 W x 125 mm D (3.64 x 1.55 x 4.93")



UWTC-REC4, \$275, shown actual size.

Convenient DIN rail mount design simplifies installation and operation with PLCs and other instrumentation.

HE-XE102, \$445, sold separately.

RAIL-35-1, \$10, sold separately.



**Note:** The UWTC-REC4 can be powered directly by the PLC or data logger you are connecting to and will not require an additional power source if the instrument has 12 to 24 Vdc @ 250 mA available for external devices. If your instrument does not have a power source available for external devices you will need to add an additional power supply (iDRN-PS-1000) to power the wireless receiver. This power supply can power up to 3 UWTC-REC4 receivers. Visit [omega.com/wireless](http://omega.com/wireless) for more information.

# Interfaces Directly with PLCs and Multi-Channel Data Loggers to Form a Complete **Wireless** Measurement and Control System!



Typical system shown above includes any 4 wireless transmitters with one **UWTC-REC4-MA** wireless receiver with analog outputs, \$275 and **HE-XE102** PLC, \$445, \$275 + 445 = \$720. (Receiver and PC only)

**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
<b>UWTC-REC4-(*)</b>	<b>\$275</b>	DIN rail wireless receiver with 4 analog outputs and alarms
<b>iDRN-PS-1000</b>	<b>150</b>	Power supply (switching) 95 to 240 Vac input, 24 Vdc output @ 850 mA (power 3 units)
<b>RAIL-35-1</b>	<b>10</b>	35 mm (1.4") DIN rail, 1 m (3.3') length
<b>RAIL-35-2</b>	<b>19</b>	35 mm (1.4") DIN rail, 2 m (6.6') length

Comes complete with measurement/data logging software, USB programming cable, and operator's manual.

\* Specify analog output signal: "V1" for 0 to 5 Vdc; "V2" for 0 to 10 Vdc, "TC" for Type K thermocouple, or "MA" for 4 to 20 mA signal.  
Ordering Example: **UWTC-REC4-MA**, 48-channel DIN rail receiver with four 4 to 20 mA outputs and alarms, \$275.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters