


# drop<sup>out</sup>

Liquid **water removal** guaranteed



Dropout Lite has all the normal features of our standard range (99.999% liquid water removal) and has been designed for those critical smaller flow rate applications where customers require addition confidence. Dropout Lite can be used in in many applications and assumes that you have already removed the bulk of condensate using additional upstream dryers or liquid water separators.

Extremely light weighing in at only 200g means it can easily be hand held. Ideal for a multitude of applications.



Product code	Flow rate					Water storage (cc)	Inlet/Outlet connection (BSPT)	Drain connection (manual BSPT)	Product dimensions (H mm x W mm)	Weight (kg)	Particulate removal (micron)
	(cfm)	(l/sec)	(l/min)	(m <sup>3</sup> /min)	(m <sup>3</sup> /hr)						
DO60A - Lite	0.04 - 2.1	0.02 - 1.0	1 - 60	0.001 - 0.06	0.06 - 3.6	24	1/4"	1/4"	160 x 40 ∅	0.2	1

Product code	Operating pressure				Operating temp				Max recommended inlet temp		Pressure drop at optimum flow rate (7 bar) (bar)	Material
	Min		Max		Min		Max		°C	°F		
	psi g	bar g	psi g	bar g	°C	°F	°C	°F				
DO60A - Lite	15	1	217	15	-5	23	80	176	35	95	0.38	Aluminium

