


FT2/FU2 Relay

- Telecom/signal relay (dry circuit, test access, ringing)
- Slim line 15x7.5mm (.59x.295")
- Switching current 2A
- 2 form C bifurcated contacts (2 CO)
- High sensitive 24V and 48V coil versions
- Meets Telcordia GR 1089, FCC Part 68 and ITU-T K20, ≥ 2500V between coil and contacts

Typical applications

Communications equipment, linecard application – analog, ISDN, xDSL, PABX, voice over IP, office and business equipment, measurement and control equipment, consumer electronics, set top boxes, HiFi, medical equipment




Approvals

UL 508 File No. E 111441
Technical data of approved types on request

Contact Data

Contact arrangement	2 Form C (CO)
Max. switching voltage	220VDC, 250VAC
Rated current	2A
Limiting continuous current	2A
Switching power	60W, 62.5VA
Contact material	PdRu, Au covered
Contact style	twin contacts
Min. recommended contact load	100µV/1µA
Initial contact resistance	<50mΩ
Thermoelectric potential	<10µV
Operate time	typ. 3ms, max. 5ms
Release time	
without diode in parallel	typ. 2ms, max. 5ms
with diode in parallel	typ. 4ms, max. 5ms
Bounce time max.	typ. 1ms, max. 5ms
Electrical endurance	
at contact application 0 (≤ 30mV/≤10mA)	min. 2.5x10 ⁶ operations
cable load open end	min. 2.0x10 ⁶ operations
resistive, 24V / 1.25A - 30W	min. 1x10 ⁵ operations
resistive, 30VDC / 2A - 60W	min. 1x10 ⁵ operations
resistive, 125VDC / 0.24A - 30W	min. 1x10 ⁵ operations
Contact ratings, UL contact rating	220VDC, 0.24A, 60W 125VDC, 0.24A, 30W 250VAC, 0.25A, 62.5VA 125VAC, 0.5A, 62.5VA 30VDC, 2A, 60W
Mechanical endurance	100x10 ⁶ operations



Coil Data

Magnetic system	monostable, non polarized
Coil voltage range	3 to 48VDC
Max. coil temperature	150°C
Thermal resistance	<125K/W


Coil versions, monostable

Coil code	Rated voltage VDC	Operate voltage VDC _{min.}	Limiting voltage VDC _{max.}	Release voltage VDC _{min.}	Coil resistance Ω±10%	Rated coil power mW
Standard version, monostable						
21	3	2.25	6.80	0.30	45	200
29	4	3.00	9.00	0.40	80	200
22	4.5	3.38	10.10	0.45	101	200
23	5	3.75	11.20	0.50	125	200
24	6	4.50	13.50	0.60	180	200
25	9	6.75	20.30	0.90	405	200
26	12	9.00	27.00	1.20	720	200
27	24	18.00	47.50	2.40	2400	240
28	48	36.00	95.00	4.80	9600	240

High dielectric version, monostable

91	3	2.25	6.80	0.30	45	200
93	5	3.75	11.20	0.50	125	200
96	12	9.00	27.00	1.20	720	200
97	24	18.00	47.50	2.40	2400	240

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



FT2/FU2 Relay (Continued)

Coil Data (continued)


Coil versions, monostable

Coil code	Rated voltage VDC	Operate voltage VDC _{min.}	Limiting voltage VDC _{max.}	Release voltage VDC _{min.}	Coil resistance Ω±10%	Rated coil power mW
71	3	2.25	5.50	0.30	30	300
73	5	3.75	9.20	0.50	83	300
76	12	9.00	22.10	1.20	480	300

High dielectric Australia version, monostable

Coil code	Rated voltage VDC	Operate voltage VDC _{min.}	Limiting voltage VDC _{max.}	Release voltage VDC _{min.}	Coil resistance Ω±10%	Rated coil power mW
71	3	2.25	5.50	0.30	30	300
73	5	3.75	9.20	0.50	83	300
76	12	9.00	22.10	1.20	480	300


All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



U_{max} upper limit of the operative range of the coil voltage (limiting voltage) when coils are continuously energized
 $U_{op.min}$ lower limit of the operative range of the coil voltage (reliable operate voltage)
 $U_{rel.min}$ lower limit of the operative range of the coil voltage (reliable release voltage)

Terminal assignment


TOP view on component side of PCB




PCB layout

TOP view on component side of PCB


THT version



SMT, long terminals



SMT, short terminals



Insulation

	standard	high dielectric
Initial dielectric strength		
between open contacts	1000V _{rms}	1500V _{rms}
between contact and coil	1500V _{rms}	4000V _{rms}
between adjacent contacts	1500V _{rms}	1800V _{rms}
Initial surge withstand voltage		
between open contacts	1500V	2500V
between contact and coil	2500V	6000V
between adjacent contacts	1500V	2500V
Initial insulation resistance		
between insulated elements	>10 ⁹ Ω	>10 ⁹ Ω
Capacitance		
between open contacts		max. 4pF
between contact and coil		max. 1pF
between adjacent contacts		max. 1pF
Cross talk at 100MHz/900MHz		-30.6dB/-13.7dB
Insertion loss at 100MHz/900MHz		-0.02dB/-0.50dB
Voltage standing wave ratio (VSWR) at 100MHz/900MHz		1.02 / 1.27

Other Data


Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customer-support/rohssupportcenter

Ambient temperature	-55°C to +85°C
Thermal resistance	<125K/W
Category of environmental protection	
IEC 61810	RT III - immersion cleanable
Degree of protection, IEC 60529	IP 67, immersion cleanable
Vibration resistance (functional)	10g, 10 to 500Hz
Shock resistance (functional), half sinus 11ms	15g
Shock resistance (destructive), half sinus 0.5ms	500g
Weight	max. 3g
Resistance to soldering heat THT	
IEC 60068-2-20	265°C/10s
Moisture sensitive level, JEDEC J-Std-020D	MSL3
Ultrasonic cleaning	not recommended
Packaging/unit	
THT version	tube/50 pcs., box/2000 pcs.
SMT short terminals	reel/500 pcs., box/2500 pcs.
SMT long terminals	reel/400 pcs., box/2000 pcs.


FT2/FU2 Relay (Continued)

Dimensions


THT version





SMT, long terminals



SMT, short terminals



Processing



FT2/FU2 Relay (Continued)

Product code structure		Typical product code	D34	02
Type	<p>D34 Signal Relays FT2 (THT) D35 Signal Relays FU2 (SMT) 2 form C, 2 CO</p>			
Coil	<p>Coil code: please refer to coil versions table Performance and coil type 2x Standard version, monostable 9x High dielectric version, monostable 7x High dielectric, Australia version, monostable (SMT version only)</p>			
Terminals	<p>Blank,(L) THT, Standard version N SMT, short pins W SMT, long pins</p>			

Product code	Arrangement	Perf. type	Coil type	Coil	Terminals	Part number
D3421	2 form C (2 CO)	Standard	Monostable	3VDC	THT	1462035-9
D3423				5VDC		1-1462035-1
D3426				12VDC		1-1462035-4
D3427	2 form C (2 CO)	Standard	Monostable	24VDC	SMT short	1-1462035-7
D3523N				5VDC		2-1462036-1
D3527N				24VDC		2-1462036-9
D3528N	2 form C (2 CO)	Standard	Monostable	48VDC	SMT long	9-1462036-3
D3521W				3VDC		1-1462036-8
D3522W				4.5VDC		2-1462036-0
D3523W	2 form C (2 CO)	High dielectric	Monostable	5VDC	THT	2-1462036-2
D3526W				12VDC		2-1462036-8
D3527W				24VDC		9-1462036-1
D3491L	2 form C (2 CO)	High dielectric	Monostable	3VDC	THT	2-1462035-7
D3493L				5VDC		2-1462035-8
D3496				12VDC		2-1462035-4
D3497				24VDC		2-1462035-5

This list represents the most common types and does not show all variants covered by this data sheet.
 Other types on request