


KEMET Part Number: C316C473M5U5TA
(C316C473M5U5TA)

Capacitor, ceramic, 0.047 uF, +/-20% Tol, 50V, Z5U, Lead Spacing=0.1"



Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.15	MAX
H	0.23	MAX
T	0.1	MAX
S	0.1	+/-0.03
LL	0.23	NOM
F	0.02	+0.004/-0.001
K	0.02	
E	0.2	NOM

Notes:

- Voltage code from part number
- EIA capacity code

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.047 uF
Lead Spacing:	0.1"
Voltage:	50V
Temperature Coefficient:	Z5U
Tolerance:	+/-20%
Application:	Commercial Standard
Temperature Range:	+10/+85C
Body Type:	Radial Conformal (Dipped)
Lead Type:	Standard Leads
Lead Form:	Crimped Out
Termination Type:	Tin

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500