


KEMET Part Number: T495B336K016ZTE350
(B45016B3369K357)

Capacitor, Tantalum, 33 uF, 3528, +/-10% Tol, 16V@85C



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.5	+/-0.2
W	2.8	+/-0.2
H	1.9	+/-0.2
K	1.4	typ
F	2.2	+/-0.1
S	0.7	+/-0.3

Notes:

-In polarity stripe, at KEMET's option, type may be indicated: see catalog for explanation of symbols

-Old part number [Obsolete] was B45016B3369K357

General Information	
Supplier:	KEMET
Part Type Description:	Molded Std Profile - Low ESR/ Surge Robust
Construction:	Standard Chip-MnO2

Specifications	
Capacitance:	33 uF
Voltage DC @ 85C:	16V
Voltage DC @ 105C:	13.36V
Voltage DC @ 125C:	10.72V
Tolerance:	+/-10%
Application:	General Purpose/Low ESR
Temperature Range:	-55/+125C
Body Type:	Molded Chip
ESR:	350 mOhm
Footprint:	3528
Termination:	Tin
RoHS:	Yes
Leakage Current:	5.3 uA
Dissipation Factor:	8%
Ripple @ 25C:	0.49 A
Ripple @ 85C:	0.441 A
Ripple @ 125C:	0.196 A

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Quantity:	2000