

Water Resistance Checker (basic) Model GSK-944

This checker utilizes resistance to measure dissolved solids in water. The more resistance, the less conductive the water; as resistance levels lessens the materials that conduct electricity are elevated. Results are displayed by a series of (8) LED's.

Technical Specifications

■ Power source: 9 VDC

■ LED resistance level indicators: 7

■ LED on/off indicator: 1■ Level adjustment: 3 levels■ PCB dimensions: 2.78 x 1.79 in.

Operating Principles

The more resistance in water the less dissolved solids, such as minerals, are present. Conversely, as resistance decreases the level of conductive material in the water increases. A series of (green, yellow, and red) LED's indicate the level of resistance (Green – higher through Red – lowest) the more LED's lit the less resistance. There are 3 switchable levels (see Figure 1 resistance table).

Circuit Assembly


Please refer to Figures 1, 2, and 3 for aid in component placement. It is recommended to start with lower components i.e. diodes, resisters, electrolyte capacitors, and transistors. Be careful to check polarity before soldering. If a problem is detected it is best too use a desoldering pump or desoldering braids to remove component. This will minimize potential damage to the printed circuit board.

Testing

Connect the battery to provide power to the circuit. The LED power light will come on. Slide switch "SW" to position "1." Insert probe into water source, LED 1 through LED 8 will display level of resistance in water source.


Troubleshooting


The main cause of problems will come from misplaced components or faulty soldering. Utilize Figures 1, 2 and 3 to ensure proper placement, polarity and then check solder points for connectivity.



Accessories

Use GSB-03 (sold separately) to house the PCB and batteries.





Resistors R1, 30 1 kΩ brown - black - red - gold R2, R8, R11, R14, R17, R20, R23, R26 brown - black - orange - gold $10 \ k\Omega$ 100 kΩ brown - black - orange - gold R4, R6, R9, R12, R15, R18, R21, R24, R27 1 ΜΩ brown - black - green - gold R5, R28 20 kΩ red - black - orange - gold R7, R19, R13, R16, R19, R22, R25, R28 green - black - red - gold 5 kΩ R31 orange - black - red - gold Electrolytic Capacitors C1, C2 33 µF Diode 5.1 V ZD1 Integrated Circuits IC1, IC2 LM339

Switch

Position 1

Water Resistance
0.98 kΩ
2.48 kΩ
4.41 kΩ
6.97 kΩ
10.57 kΩ
15.96 kΩ

Position 2

LED	Water Resistance
8	18.83 kΩ
7	33.80 kΩ
6	53.06 kΩ
5	78.74 kΩ
4	114.61 kΩ
3	168.61 kΩ
2	258.48 kΩ
1	438.22 kΩ

Position 3

LED	Water Resistance
8	197.26 kΩ
7	347.04 kΩ
6	539.62 kΩ
5	796.39 kΩ
4	1,155.86 kΩ
3	1,695.08 kΩ
2	2,593.77 kΩ
1	4,391.16 kΩ