


KEMET Part Number: C330C472J2G5TA
(C330C472J2G5TA)

Capacitor, ceramic, 4700 pF, +/-5% Tol, 200V, COG, Lead Spacing=0.2"



Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.3	MAX
H	0.36	MAX
T	0.15	MAX
S	0.2	+/-0.03
LL	0.276	MIN
F	0.02	+0.004/-0.001
K	0.02	

Notes:

-Voltage code from part number

-TC/Dielectric code from part number

General Information

Supplier: KEMET

Specifications

Capacitance:	4700 pF
Lead Spacing:	0.2"
Voltage:	200V
Temperature Coefficient:	COG
Tolerance:	+/-5%
Application:	Commercial Standard
Temperature Range:	-55/+125C
Body Type:	Radial Conformal (Dipped)
Lead Type:	Standard Leads
Lead Form:	Straight
Termination Type:	Tin (Sn)

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	250