

KEMET Part Number: C0603C120J5GACTU
(C0603C120J5GAC7867)

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 12 pF, +/-5% Tol, 50V, COG, 0603



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.60	+/-0.15
W	0.80	+/-0.15
T	0.80	+/-0.07
B	0.35	+/-0.15
S	0.7	MIN

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Type:	Paper Tape
Package Quantity:	4000

General Information	
Supplier:	KEMET
Part Type Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Miscellaneous Electrical:	Note: KEMET 50V rated parts may be operated at 63 Volts

Specifications	
Capacitance:	12 pF
Chip Size:	0603
Voltage:	50V
Temperature Coefficient:	COG
Tolerance:	+/-5%
Application:	Standard Chip
Termination Type:	Tin
Marked:	No
Temperature Range:	-55/+125C
Dissipation Factor:	0.1%
Insulation Resistance:	100 GOhm
Dielectric Strength:	125V