

# Thermodata Components

## High Barrier Terminal Strips

### Technical Data

<b>Number Of Ways</b>	2 to 12
<b>Current Rating</b>	15 amps
<b>Working Voltage</b>	750 V d.c or a.c. peak
<b>Insulation resistance</b>	Greater than 10,000 megaohms
<b>Temperature Range</b>	-55°C to + 100°C



### Materials and finishes

<b>Moulding</b>	High impact thermoplastic UL 94V-0 rated
<b>Terminal Plates</b>	Brass, nickel plated
<b>Terminal Tags</b>	Brass, tin plated
<b>Screws</b>	6/32 UNC Binder head, nickel plated


### RoHS Compliant



Twin Terminals




Drop-Through Solder Terminals



### Dimensions

Number Of Terminals	Mounting Hole Centers
2	28.6
3	38.1
4	47.6
5	57.2
6	66.7
7	76.2
8	85.7
9	95.2
10	104.8
11	114.3
12	123.8



## Ordering Information

### Twin Terminals

Please quote part number

R44    18    000  
↑↑  
Specify number of ways

### Drop Through Solder Terminals

Please quote part number

R44    25    000  
↑↑  
Specify number of ways

**© Thermodata Components - All Rights Reserved**  
**PO Box 140, Sandy, SG19 2WL.**  
**Telephone: +44 (0) 1767 683697    Fax: +44 (0) 1767 683347**  
**Email: [sales@thermodata.co.uk](mailto:sales@thermodata.co.uk)**