


## Ceramic AC Capacitors Class X1, 760 V<sub>AC</sub>/Class Y1, 500 V<sub>AC</sub>



Dimensions in mm

**Note**

Impedance (Z) as a function of frequency (f) at T<sub>a</sub> = 20 °C (average).  
Measurement with lead length 6 mm.



I = f (U<sub>R</sub>) (typ.)



**DESIGN**

Disc capacitors with epoxy coating

**RATED VOLTAGE U<sub>R</sub>**

- (X1): 760 V<sub>AC</sub>, 50 Hz (IEC 60384-14.2)
- (Y1): 500 V<sub>AC</sub>, 50 Hz (IEC 60384-14.2)
- 250 V<sub>AC</sub>, 60 Hz (UL1414, CSA C22.2)

**DIELECTRIC STRENGTH BETWEEN LEADS**

- Component test:
- 4000 V<sub>AC</sub>, 50 Hz, 2 s
- As repeated test admissible only once with:
- 3600 V<sub>AC</sub>, 50 Hz, 2 s
- Random sampling test (destructive test):
- 4000 V<sub>AC</sub>, 50 Hz, 60 s

**DIELECTRIC STRENGTH OF BODY INSULATION**

4000 V<sub>AC</sub>, 50 Hz, 60 s (destructive test)

**DISSIPATION FACTOR tan δ**

≤ 25 x 10<sup>-3</sup>

**INSULATION RESISTANCE R<sub>IS</sub>**

≥ 10 x 10<sup>9</sup> Ω

**CATEGORY TEMPERATURE RANGE θ<sub>A</sub>**

(- 40 to + 125) °C

**CLIMATIC CATEGORY ACC. TO EN60068-1**

40/125/21


**COATING**

Epoxy dipped, insulating, flame retarding acc. to UL 94V-0

**TAPING AND SPECIAL LEAD CONFIGURATIONS**

On request

**MARKING**



WKP 33 pF to 1.5 nF

WKP 2.2 nF to 4.7 nF

**Note**

- All approval marks are also shown on the label.

<b>ORDERING INFORMATION, CERAMIC X1/Y1 CAPACITORS WKP</b>							
CAPACITANCE <sup>(2)</sup> (pF)	TOL. (%)	D x s (mm)	F ± 1 <sup>(1)</sup> (mm)	d ± 0.05 <sup>(1)</sup> (mm)	V ± 0.5 <sup>(1)</sup> (mm)	ORDERING CODE	
<b>CLASS 1 N 750</b>							
33	± 10 , ± 20	8.0 x 6.0	12.5	0.6	1.9	WKP330□CP□□□KR	
<b>CLASS 2 K 1200</b>							
47	± 10 , ± 20	8.0 x 6.0	12.5	0.6	2.3	WKP470□CP□□□KR	
68						WKP680□CP□□□KR	
<b>CLASS 2 K 1500</b>							
100	± 10 , ± 20	8.0 x 6.0	12.5	0.6	2.3	WKP101□CP□□□KR	
<b>CLASS 2 K 2000</b>							
150	± 10 , ± 20	8.0 x 6.0	12.5	0.6	2.3	WKP151□CP□□□KR	
220						WKP221□CP□□□KR	
<b>CLASS 2 K 4000</b>							
330	± 10 , ± 20	8.0 x 6.0	12.5	0.6	2.5	WKP331□CP□□□KR	
470		9.0 x 6.0				WKP471□CP□□□KR	
680		10.0 x 6.0				WKP681□CP□□□KR	
1000		12.0 x 6.0				WKP102□CP□□□KR	
1500		13.0 x 6.0				WKP152□CP□□□KR	
2200		15.0 x 6.0		WKP222□CP□□□KR			
3300		16.0 x 6.0		WKP332□CP□□□KR			
3900		18.0 x 6.0		WKP392□CP□□□KR			
4700					0.8	2.7	WKP472□CP□□□KR

**Notes**

- <sup>(1)</sup> Standard lead configuration, other lead spacing and diameter available on request.
- <sup>(2)</sup> Capacitance values from 470 pF to 4700 pF: The alternative usage of smaller VKP series is recommended for new application.

<b>ORDERING CODE</b>			
□	7 <sup>th</sup> digit	Capacitance Tolerance:	± 10 % = K ± 20 % = M
□□□	10 <sup>th</sup> to 12 <sup>th</sup> digit	Lead Configuration (see General Information)	
R	14 <sup>th</sup> digit	RoHS Compliant Component	

<b>APPROVALS</b>						
<b>IEC 60384 - 14 / 2<sup>nd</sup> Issue (1993) incl. Am. 1 (1995) - Safety Tests</b>						
<b>EN 132 400 (1994) - Safety Tests</b>						
<b>THAT APPROVAL TOGETHER WITH THE CB TEST CERTIFICATE SUBSTITUTES THE NATIONAL APPROVAL OF THE FOLLOWING</b>						
Belgium	France	Italy	Austria	China	Japan	Spain
Denmark	Greece	Luxembourg	Portugal	Singapore	Poland	United
Germany	Ireland	Netherlands	Sweden	Slovenia	Hungaria	Czech Republic
Finland	Iceland	Norway	Switzerland	Korea	Israel	
Y1 - Capacitor: CB-Test Certificate: DE-1-11002-A1				33 pF ... 4.7 nF	500 V <sub>AC</sub>	
X1 - Capacitor: CB-Test Certificate: DE-1-11002-A1				33 pF ... 4.7 nF	760 V <sub>AC</sub>	
Minimum thickness of insulation: 0.4 mm						
<b>UNDERWRITERS LABORATORIES INC.</b>						
<b>UL 1414</b>	Across-the-line, Antenna-coupling and Line-by-pass component.			33 pF ... 4.7 nF	250 V <sub>AC</sub>	
<b>CANADIAN STANDARDS ASSOCIATION</b>						
<b>CSA C22.2</b>	Across-the-line, antenna-coupling and line-by-pass component			33 pF ... 4.7 nF	250 V <sub>AC</sub>	
<b>NO 1-98</b>	Agency Files / Licences			E 183 844 V1 S1		

<b>ORDERING INFORMATION</b>						
<u>WKP</u>	<u>221</u>	<u>M</u>	<u>CP</u>	<u>ED0</u>	<u>K</u>	<u>R</u>
SERIES	CAP. VALUE	TOLERANCE	RATED VOLTAGE	LEAD CONFIGURATION	INTERNAL CODE	ROHS COMPLIANT



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**