

TPN3021

Tripolar overvoltage protection for network interfaces

Features

- Triple crowbar protection
- Low capacitance
- Low holding current: I_H = 30 mA minimum
- Surge current:
 I_{PP} = 200 A, 2/10 μs
 I_{PP} = 30 A, 10/1000 μs

Benefits

- Trisil[™] technology is not subject to ageing and provides a fail safe mode in short circuit for a better protection.
- This device can be used to help equipment to meet main standards such as UL1950, IEC 950 / CSA C22.2 and UL1459.
- Trisils have UL94 V0 approved resin.
- SO8 package is JEDEC registered.
- Trisils comply with the following standards GR-1089 Core, ITU-T-K20/K21, VDE0433, VDE0878, IEC 61000-4-2.

Applications

Dedicated to data line protection, this device provides a tripolar protection function. It ensures the same protection capability with the same breakdown voltage in both common and differential modes.





Figure 1. Schematic diagram



Description

The TPN is a low capacitance transient surge arrestor designed for protection of high debit rate communication networks. Its low capacitance avoids distorsion of the signal as it has been designed for T1/E1 and Ethernet networks.

TM: Trisil is a trademark of STMicroelectronics

1 Characteristics

	Peak surge voltage (V)	Voltage waveform (μs)	Required peak current (A)	Current waveform (µs)	Minimum serial resistor to meet standard (Ω)
GR-1089-CORE First level	2500 1000	2/10 10/1000	500 100	2/10 10/1000	7.5 25
GR-1089-CORE Intrabuilding	1500	2/10	100	2/10	0
ITU-T-K20/K21	1000	10/700	25	25 5/310	
ITU-T-K20 (IEC 61000-4-2)	6000 8000	1/60 ns		t discharge discharge	
VDE0433	4000 2000	10/700	100 50	5/310	40 0
VDE0878	4000 2000	1.2/50	100 50	1/20	0 0
IEC 61000-4-5	2000 2000	10/700 1.2/50	50 50	5/310 8/20	0 0

Table 1. Compliant with the following standards

Table 2.Absolute ratings ($T_{amb} = 25 \ ^{\circ}C$)

Symbol	Parameter		Value	Unit
I _{PP}	Peak pulse current: t _r / t _p	10/1000 8/20 10/560 5/310 10/160 1/20 2/10	30 100 40 50 75 100 200	A
1	Non repetitive surge peak on-state current One cycle	50 Hz 60 Hz	8 9	A
ITSM	Non repetitive surge peak on-state current (F = 50Hz)	3 1.5	А	
T _{stg}	Storage temperature range		-55 to +150	°C
Тj	Operating junction temperature range		-40 to +150	°C
ΤL	Maximum lead temperature for soldering during 10s		260	°C

Table 3.Thermal resistances

Symbol	Parameter	Value	Unit
R _{th(j-a)}	Junction to ambient	170	°C/W



Table 4.	Electrical characteristics - demitions ($T_{amb} = 25 C$
Symbol	Parameter	
V _{RM}	Stand-off voltage	
I _{RM}	Leakage current at stand-off voltage	'pp
V _R	Continuos Reverse voltage	I _{BO}
V _{BR}	Breakdown voltage	
V _{BO}	Breakover voltage	V _{RM} V _R V _{BR} V _{BO}
Ι _Η	Holding current	RM ^v R ^v BR ^v BO
I _{BO}	Breakover current	
I _R	Continuos reverse voltage	
I _{PP}	Peak pulse current	
С	Capacitance	

Table 4.Electrical characteristics - definitions ($T_{amb} = 25^{\circ}$ C)

Table 5. Static parameters

Order code	I _{RM} max. @ V _{RM}		V _{BO} ⁽¹⁾ m	ax.@ I _{BO}	l _H ⁽²⁾ min.	C ⁽³⁾ typ.	
Order Code	μA	v	v	mA	mA	pF	
TPN3021	4	28	38	300	30	16	

1. See Figure 6: Test circuit 1 for IBO and VBO parameters.

2. See Figure 7: Test circuit 2 for dynamic IH parameter

3. $V_{R} = 0 V \text{ bias}, V^{RMS} = 1 V, F = 1 MHz$

Figure 2. Pulse waveform

Figure 3.	Non repetitive surge peak on-state
	current versus overload duration
	(T _i initial = 25 °C)








Figure 4. Variation of junction capacitance versus reverse voltage applied (typical values)






2 Test circuits

2.1 Test procedure for test circuit 1

Figure 6. Test circuit 1 for I_{BO} and V_{BO} parameters



Pulse test duration ($t_p = 20 \text{ ms}$):

- For bidirectional devices = switch K is closed
- For unidirectional devices = switch K is open

V_{OUT} selection:


Device with V_{BO} < 200 V, V_{OUT} = 250 V_{RMS}, R1 = 140 Ω

Device with $V_{BO} \geq$ 200 V, V_{OUT} = 480 $V_{RMS},~R2$ = 240 Ω



2.2 Test procedure for test circuit 2

Figure 7. Test circuit 2 for dynamic I_H parameter




This is a go no-go test, which can confirm the holding current (I_H) level.

Procedure

- 1. Adjust the current level at the I_{H} value by short circuiting the AK of the D.U.T.
- 2. Fire the D.U.T. with a surge current I_{PP} = 10A, 10/1000 $\mu s.$
- 3. The D.U.T. will come back off-state within 50 ms maximum.



3 Ordering information scheme



	TPN 30 2 1 RL
Tripolar protection for networks	
Numerical code	
Version	
Package 1 = SO-8 plastic	
Packing RL = Tape and reel Blank = Tube	




4 Package information


- Epoxy meets UL94, V0
- Lead-free package

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: <u>www.st.com</u>. ECOPACK[®] is an ST trademark.

Table 6. SO-8 dimensions



Footprint, dimensions in mm (inches)



5 Ordering information

Table 7. Ordering information

Ordering code	Marking	Package	Weight	Base qty	Delivery mode
TPN3021	TPN302	SO-8	0.08g	100	Tube
TPN3021RL ⁽¹⁾	TPN302		0.009	2500	Tape and reel

1. Preferred device

6 Revision history

Table 8.Document revision history

Date	Revision	Changes
Sep-2001	3	Previous release
07-Feb-2006	4	Reformatted to current template. Maximum junction temperature parameter replaced by Operating junction temperature range in Table 3. Added footnote 1 to Ordering information table.
25-Jun-2010	5	Updated trademark statement.



Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2010 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com



Doc ID 4143 Rev 5