


Number of contacts

4/2 +



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	<b>09 12 006 3041</b>	<b>09 12 006 3141</b>	<p>Contact arrangement view from termination side</p>	

Identification	Wire gauge (mm²)	Part number		Drawing	Dimensions in mm																																			
		Male contact	Female contact																																					
Crimp contacts  Han® C contacts Power contacts silver plated  	1.5 2.5 4 6	<b>09 32 000 6104</b> <b>09 32 000 6105</b> <b>09 32 000 6107</b> <b>09 32 000 6108</b>	<b>09 32 000 6204</b> <b>09 32 000 6205</b> <b>09 32 000 6207</b> <b>09 32 000 6208</b>	<table border="1"> <thead> <tr> <th colspan="2">Wire gauge</th> <th>∅</th> <th colspan="2">Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5</td> <td>mm²</td> <td>AWG 16</td> <td>1.75</td> <td>9.5 mm</td> </tr> <tr> <td>2.5</td> <td>mm²</td> <td>AWG 14</td> <td>2.25</td> <td>9.5 mm</td> </tr> <tr> <td>4</td> <td>mm²</td> <td>AWG 12</td> <td>2.85</td> <td>9.5 mm</td> </tr> <tr> <td>6</td> <td>mm²</td> <td>AWG 10</td> <td>3.5</td> <td>9.5 mm</td> </tr> </tbody> </table>	Wire gauge		∅	Stripping length		1.5	mm²	AWG 16	1.75	9.5 mm	2.5	mm²	AWG 14	2.25	9.5 mm	4	mm²	AWG 12	2.85	9.5 mm	6	mm²	AWG 10	3.5	9.5 mm											
Wire gauge		∅	Stripping length																																					
1.5	mm²	AWG 16	1.75	9.5 mm																																				
2.5	mm²	AWG 14	2.25	9.5 mm																																				
4	mm²	AWG 12	2.85	9.5 mm																																				
6	mm²	AWG 10	3.5	9.5 mm																																				
Han D® contacts Signal contacts  silver plated  	0.14-0.37 0.5 0.75 1 1.5 2.5	<b>09 15 000 6104</b> <b>09 15 000 6103</b> <b>09 15 000 6105</b> <b>09 15 000 6102</b> <b>09 15 000 6101</b> <b>09 15 000 6106</b>	<b>09 15 000 6204</b> <b>09 15 000 6203</b> <b>09 15 000 6205</b> <b>09 15 000 6202</b> <b>09 15 000 6201</b> <b>09 15 000 6206</b>	<table border="1"> <thead> <tr> <th colspan="2">Wire gauge</th> <th>∅</th> <th colspan="2">Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37</td> <td>mm²</td> <td>AWG 26-22</td> <td>0.9</td> <td>8 mm</td> </tr> <tr> <td>0.5</td> <td>mm²</td> <td>AWG 20</td> <td>1.1</td> <td>8 mm</td> </tr> <tr> <td>0.75</td> <td>mm²</td> <td>AWG 18</td> <td>1.3</td> <td>8 mm</td> </tr> <tr> <td>1</td> <td>mm²</td> <td>AWG 18</td> <td>1.45</td> <td>8 mm</td> </tr> <tr> <td>1.5</td> <td>mm²</td> <td>AWG 16</td> <td>1.75</td> <td>8 mm</td> </tr> <tr> <td>2.5</td> <td>mm²</td> <td>AWG 14</td> <td>2.25</td> <td>6 mm</td> </tr> </tbody> </table>	Wire gauge		∅	Stripping length		0.14-0.37	mm²	AWG 26-22	0.9	8 mm	0.5	mm²	AWG 20	1.1	8 mm	0.75	mm²	AWG 18	1.3	8 mm	1	mm²	AWG 18	1.45	8 mm	1.5	mm²	AWG 16	1.75	8 mm	2.5	mm²	AWG 14	2.25	6 mm	
Wire gauge		∅	Stripping length																																					
0.14-0.37	mm²	AWG 26-22	0.9	8 mm																																				
0.5	mm²	AWG 20	1.1	8 mm																																				
0.75	mm²	AWG 18	1.3	8 mm																																				
1	mm²	AWG 18	1.45	8 mm																																				
1.5	mm²	AWG 16	1.75	8 mm																																				
2.5	mm²	AWG 14	2.25	6 mm																																				
gold plated  	0.14-0.37 0.5 0.75 1 1.5 2.5	<b>09 15 000 6124</b> <b>09 15 000 6123</b> <b>09 15 000 6125</b> <b>09 15 000 6122</b> <b>09 15 000 6121</b> <b>09 15 000 6126</b>	<b>09 15 000 6224</b> <b>09 15 000 6223</b> <b>09 15 000 6225</b> <b>09 15 000 6222</b> <b>09 15 000 6221</b> <b>09 15 000 6226</b>																																					

Stock items in bold type

Han Q