

March 2013

FQA36P15 / FQA36P15_F109 P-Channel QFET MOSFET

-150 V, -36 A, 90 mΩ


Description

This P-Channel enhancement mode power MOSFET is produced using Fairchild Semiconductor®'s proprietary planar stripe and DMOS technology. This advanced MOSFET technology has been especially tailored to reduce on-state resistance, and to provide superior switching performance and high avalanche energy strength. These devices are suitable for switched mode power supplies, audio amplifier, DC motor control, and variable switching power applications.

Features

- -36 A, -150 V, $R_{DS(on)}$ = 90 m Ω (Max) @V $_{GS}$ = -10 V, I_D = -18 A
- Low Gate Charge (Typ. 81 nC)
- Low Crss (Typ. 110 pF)
- · 100% Avalanche Tested
- 175°C Maximum Junction Temperature Rating





Absolute Maximum Ratings

Symbol	Parameter		FQA36P15	Unit	
V _{DSS}	Drain-Source Voltage		-150	V	
I _D	Drain Current - Continuous (T _C = 25°C)		-36	А	
	- Continuous (T _C = 100°C)		-25.5	А	
I _{DM}	Drain Current - Pulsed	(Note 1)	-144	А	
V _{GSS}	Gate-Source Voltage		± 30	V	
E _{AS}	Single Pulsed Avalanche Energy	(Note 2)	1400	mJ	
I _{AR}	Avalanche Current	(Note 1)	-36	А	
E _{AR}	Repetitive Avalanche Energy	(Note 1)	29.4	mJ	
dv/dt	Peak Diode Recovery dv/dt	(Note 3)	-5.0	V/ns	
P _D	Power Dissipation (T _C = 25°C)		294	W	
	- Derate above 25°C		1.96	W/°C	
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to +175	°C	
T _L	Maximum lead temperature for soldering purposes, 1/8" from case for 5 seconds		300	°C	

Thermal Characteristics

Symbol	Parameter	Тур	Max	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case		0.51	°C/W
$R_{\theta CS}$	Thermal Resistance, Case-to-Sink	0.24		°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient		40	°C/W

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FQA36P15	FQA36P15	TO-3PN			30
FQA36P15	FQA36P15_F109	TO-3PN			30

Electrical Characteristics $T_C = 25$ °C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
Off Charac	teristics	1		+		-
BV _{DSS}	Drain-Source Breakdown Voltage	V_{GS} = 0 V, I_{D} = -250 μ A	-150			V
$\Delta BV_{DSS}/$ ΔT_J	Breakdown Voltage Temperature Coefficient	I_D = -250 μA, Referenced to 25°C		-0.13		V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = -150 V, V _{GS} = 0 V			-10	μА
		V _{DS} = -120 V, T _C = 150°C			-100	μА
I _{GSSF}	Gate-Body Leakage Current, Forward	V _{GS} = -25 V, V _{DS} = 0 V			-100	nA
I _{GSSR}	Gate-Body Leakage Current, Reverse	V _{GS} = 25 V, V _{DS} = 0 V			100	nA
On Charact	eristics					
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$	-2.0		-4.0	V
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} = -10 V, I _D = -18A		0.076	0.09	Ω
9 _{FS}	Forward Transconductance	V _{DS} = -40 V, I _D = -18A (Note 4)		19.5		S
Dynamic Ch	naracteristics				I.	
C _{iss}	Input Capacitance	$V_{DS} = -25 \text{ V}, V_{GS} = 0 \text{ V},$		2550	3320	pF
C _{oss}	Output Capacitance	f = 1.0 MHz		710	920	pF
C _{rss}	Reverse Transfer Capacitance	-		110	140	pF
Switching C	Characteristics					
t _{d(on)}	Turn-On Delay Time	$V_{DD} = -75 \text{ V}, I_{D} = -36\text{A},$		50	110	ns
t _r	Turn-On Rise Time	$R_G = 25 \Omega$		350	710	ns
$t_{d(off)}$	Turn-Off Delay Time	(1)-1-4 (5)		155	320	ns
t _f	Turn-Off Fall Time	(Note 4, 5)		150	310	ns
Qg	Total Gate Charge	$V_{DS} = -120 \text{ V}, I_{D} = -36\text{A},$		81	105	nC
Q _{gs}	Gate-Source Charge	V _{GS} = -10 V		19		nC
Q _{gd}	Gate-Drain Charge	(Note 4, 5)		42		nC
Drain-Source	ce Diode Characteristics and Maximum Ratings				I.	
I _S	S Maximum Continuous Drain-Source Diode Forward Current				-36	Α
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current				-144	Α
V_{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S =-36A			-4.0	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0 V, I _S = -36 A,		198		ns
Q _{rr}	Reverse Recovery Charge	$dI_F / dt = 100 A/\mu s $ (Note 4)		1.45		μС

NOTES

^{1.} Repetitive Rating : Pulse width limited by maximum junction temperature

^{2.} L = 1.45mH, I $_{AS}$ =-36A, V $_{DD}$ = -50V, R $_{G}$ = 25 Ω , Starting T $_{J}$ = 25°C

^{3.} $I_{SD} \le$ -36A, di/dt \le 300A/ μ s, $V_{DD} \le$ BV $_{DSS}$, Starting T_J = 25°C

^{4.} Pulse Test : Pulse width $\leq 300 \mu \text{s}, \, \text{Duty cycle} \leq 2\%$

^{5.} Essentially independent of operating temperature

Typical Performance Characteristics

Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs.

Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperatue





Figure 6. Gate Charge Characteristics



Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 8. On-Resistance Variation vs. Temperature




Figure 9. Maximum Safe Operating Area

Figure 10. Maximum Drain Current vs. Case Temperature







Figure 11. Transient Thermal Response Curve




Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms







Unclamped Inductive Switching Test Circuit & Waveforms







Peak Diode Recovery dv/dt Test Circuit & Waveforms









Mechanical Dimensions (Continued) TO-3PN 5.00 4.60 15,80 15,40 (R0.50) -20.10 19.70 18.90 18.50 (1.85)2.20 1.80 2.60 2.20 20.30 19.70 3,20 2,80 **⊕** Ø0.55**⋈** 1.20 0.80 1 0.75 0.55 5.45 5,45 (R0,50)

Dimensions in Millimeters





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

2Cool™ FPS™ AccuPower™ F-PFS™ FRFET® AX-CAP® BitSiC™ Global Power ResourceSM

Build it Now™ Green Bridge™ CorePLUS™ Green FPS™ Green FPS™ e-Series™ CorePOWER™

Gmax™ $CROSSVOLT^{\text{TM}}$ CTL™ GTO™ Current Transfer Logic™ IntelliMAX™ DEUXPEED® ISOPLANAR™

Dual Cool™ Marking Small Speakers Sound Louder EcoSPARK® and Better™

MegaBuck™ EfficentMax™ ESBC™ MICROCOUPLER™ MicroFET™

MicroPak™ MicroPak2™ Fairchild® MillerDrive™ Fairchild Semiconductor® MotionMax™ FACT Quiet Series™ mWSaver™

FACT® FAST® OptoHiT™ OPTOLOGIC® FastvCore™ OPTOPLANAR® FETBench™

PowerTrench® PowerXS™

Programmable Active Droop™

OFET QS™

R

Quiet Series™ RapidConfigure™ TM

ng our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

SPM[®] STEALTH™ SuperFET® SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS® SyncFET™

SYSTEM ®* TinyBoost³ TinyBuck™ TinyCalc™ TinyLogic[®] TINYOPTO™ TinyPower™ TinyPWM™ TinyWire™ TranSiC® TriFault Detect™ TRUECURRENT®*

Svnc-Lock™

μSerDes™ Ultra FRFET™ UniFET™ VCXTM VisualMax™ VoltagePlus™ XS™

*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN. WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY
FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild of from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS **Definition of Terms**

Datasheet Identification	Product Status	Definition		
Advance Information Formative / In Design		Datasheet contains the design specifications for product development. Specification may change in any manner without notice.		
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.		
No Identification Needed Full Production Datasheet contains final specifications. Fair make changes at any time without notice to		Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.		
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.		

Rev. 164