

SPECTRACOOL™ Compact Indoor



N17 115/230 Volt
1000 BTU/Hr.
293 Watt

N17 460 Volt
1800 BTU/Hr.
527 Watt

Industry Standards

UL/cUL Listed; Type 12; File No. SA6453

CE
IP 54 Internal Loop
IP 34 on External Loop

Application

- Industrial automation
- Package handling equipment
- Security and defense systems

Features

- Narrow design accommodates 12-in. deep cabinets
- R134a earth-friendly refrigerants
- Models for 115, 230 and 400/460 VAC power input
- UL Listed to save customers time and money with agency approvals
- Attractive industrial design with minimal use of visible fasteners
- Reliable mechanical thermostat is located behind the cover of the unit; Air Conditioner models include digital display on ambient side
- Galvanized sheet-metal cover for rugged factory environments
- Easy-mount flanges for simple installation
- Cut-out adapter options for enclosures with McLean GENESIS® air conditioners enable users to easily transition to the new unit

- Dust-resistant condenser coil allows the unit to be run filterless in most applications
- Cleanable, reusable aluminum mesh filter protects coils for maximum cooling performance
- Mounting hardware, gaskets and user manual furnished with the unit
- Every unit functionally tested before shipping
- Standard Indoor Air Conditioner models also include:
 - Active condensate management with heater strip
 - Power-off relay for door switch and other system requirements
 - Malfunction switch

Specifications

- Nominal cooling capacity:
 - N17 1000 BTU/Hr. (293 W)
 - N17 1800 BTU/Hr. (527 W)
- Operating temperature range from 50 F/10 C to 125 F/52 C

Finish

- RAL 7035 light-gray, semi-textured powder-coat paint
- Other colors and textures available



Notes

Visit www.McLeanCoolingTech.com to download 2D and 3D CAD drawings into the overall design of your electronic system.

Performance Data **N17 Models 1000/1800 BTU/Hr. (300/527 Watt)**


CATALOG NUMBER						
Indoor Model	N170116G010	N170126G010	N170146G010	N170216G010	N170226G010	N170246G010
COOLING PERFORMANCE						
Nominal:						
BTU/Hr.	908/1025	908/1025	908/1025	1500/1800	1500/1800	1500/1800
Watts	266/300	266/300	266/300	440/527	440/527	440/527
Refrigerant	R-134a	R-134a	R-134a	R-134a	R-134a	R-134a
Refrigerant Charge (ounces/grams)	5/142	5/142	5/142	5.5/156	5.5/156	5.5/156
Operating Temperature Range:						
Maximum (°F/°C)	125/52	125/52	125/52	125/52	125/52	125/52
Minimum (°F/°C)	50/10	50/10	50/10	50/10	50/10	50/10
Airflow at 0 Static Pressure:						
Internal loop 50 Hz (CFM / m ³ /hr.)	57/97	57/97	57/97	61/104	61/104	61/104
External loop 50 Hz (CFM / m ³ /hr.)	96/163	96/163	96/163	98/167	98/167	98/167
Internal loop 60 Hz (CFM / m ³ /hr.)	67/114	67/114	67/114	72/122	72/122	72/122
External loop 60 Hz (CFM / m ³ /hr.)	114/194	114/194	114/194	118/200	118/200	118/200
ELECTRICAL DATA						
Rated Voltage	110/115	220/208-230	400/460	110/115	220/208-230	400/460
Frequency (Hz)	50/60	50/60	50/60	50/60	50/60	50/60
Operating Range	+/- 10%	+/- 10%	+/- 10%	+/- 10%	+/- 10%	+/- 10%
Max. Power Consumption (W at 50/60 Hz)	337/356	375/407	345/376	642/728	639/667	543/603
Max. Nominal Current (A at 50/60 Hz)	4.4/3.9	2.3/2.1	1.2/1.2	7.0/7.1	4.0/3.5	2.0/2.0
Starting Current (A)	18	8.5	4.25	28	14.4	7.2
Agency Approvals	UL/cUL Listed CE					
Power Input Description	Terminal Block					
ENCLOSURE PROTECTION						
UL Type	Type 12					
IP	IP 54					
CONTROLLER (...G010 Models)						
Thermostat Location	Behind Cover, Right Side					
Factory Thermostat Setting (°F/°C)	80/27					
CONTROLLER (...G020 Models)						
Thermostat Location	Ambient Side					
Factory Thermostat Setting (°F/°C)	80/27					
SOUND LEVEL						
At 1.5 Meters	6.5 dBA					
UNIT CONSTRUCTION						
Material	Galvanized sheet metal standard					
Finish	RAL 7035 light-gray, semi-textured powder-coat paint standard Other colors available					
UNIT DIMENSIONS						
Height (in./mm)	17.64/448.1	17.64/448.1	22.14/562.4	17.64/448.1	17.64/448.1	22.14/562.4
Width (in./mm)	12.0/304.8	12.0/304.8	12.0/304.8	12.0/304.8	12.0/304.8	12.0/304.8
Depth (in./mm)	8.4/213.4	8.4/213.4	8.4/213.4	8.4/213.4	8.4/213.4	8.4/213.4
Weight (lb./kg)	50/23	50/23	66/30	54/25	54/25	73/33

Performance Curves for N17 Models 1000 BTU/Hr. (293 Watt)




Performance Curves for N17 Models 1000/2000 BTU/Hr. (293/585 Watt)

N17-01(2/4)6-GXXX Capacity Curves at 50 Hz




N17-01(2/4)6-GXXX Capacity Curves at 60 Hz




Performance Curves for N17 Models 1000 BTU/Hr. (293 Watt)

N17-0216-GXXX Capacity Curves at 50 Hz




N17-0216-GXXX Capacity Curves at 60 Hz




Performance Curves for N17 Models 1000/2000 BTU/Hr. (293/585 Watt)


N17-02(2/4)6-GXXX Capacity Curves at 50 Hz



N17-02(2/4)6-GXXX Capacity Curves at 60 Hz



N17 Models 1000/1800 BTU/Hr. (300/527 Watt)



Visit www.McLeanCoolingTech.com to download 2D and 3D CAD drawings into the overall design of your electronic system.

Notes