



ISSUE 3; December 2012 - RoHS 2011/65/EU



Description

- Suitable for real time clock applications
- 32.768kHz output crystal oscillators
- Ceramic package with a seam sealed metal lid, hermetically sealed

Frequency Range

- Frequency 32.7680kHz

Supply Voltage

- Voltage 2.5V ±5%

Ageing

- Ageing ±3ppm max per year

Output Compatibility & Load

- Output Compatibility CMOS
- Drive Capability 15pF max

Frequency Stabilities

- Frequency Stability ±20ppm, ±25ppm ±50ppm, ±100ppm
(inclusive of supply voltage and output load variations over the operating temperature range)

Operating Temperature Ranges

- 0 to 70°C
- -40 to 85°C

Output Details


- Logic '1' to pad 1 enables oscillator output
- Logic '0' to pad 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state
- No connection to pad 1 enables oscillator output

Environmental Parameters


- Storage Temperature Range: -55 to 125°C
- Shock: MIL-STD-883F, Method 2002.4: 1500G, 0.5ms, 3 times in each of 3 mutually perpendicular planes.
- Vibration: MIL-STD-883F, Method 2007.3: 20G (20Hz-2000Hz), 1.52mm amplitude

Ordering Information (*minimum required)

- Frequency*
- Model*
- Output
- Frequency Stability*
- Operating Temperature Range*
- Supply Voltage
- Example
- 32.768kHz CFPS-108
- CMOS ±50ppm 0 to 70C 2.5V




Outline (mm)




- Pad Connections
1. Tri-State Operation
 2. GND
 3. Output
 4. +Vs

Solder Pad Layout



Test Circuit



* Inclusive of jigging and equipment capacitance

Sales Office Contact Details:

UK: +44 (0)1460 270200
 Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18
 USA: +1 (0)408.273.4530


Email: info@iqdfrequencyproducts.com
 Web: www.iqdfrequencyproducts.com



Packing Details

- Pack Style: **Bulk** Loose in bulk pack
Pack Size 100
- Pack Style: **Reel** Tape and reel in accordance with EIA-481-D
Pack Size 1,000
- Alternative packing options available

Wave Form



Electrical Specification - maximum limiting values 2.5V ±5%

Frequency Range	Temp Range	Stability Inclusive		Current Draw	Rise & Fall (10 to 90%)	Duty Cycle %
		Min	Max			
32.768kHz	0 to 70°C	±20ppm	±100ppm	2.5mA	50ns	40/60%
	-40 to 85°C	±25ppm	±100ppm	2.5mA	50ns	40/60%

This document was correct at the time of printing; please contact your local sales office for the latest version

Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18
USA: +1 (0)408.273.4530

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com