


US Power Supply Cord Hospital Grade with IEC Connector C13, V-Lock



new

**Description**

1 Function:

- Power Cord,
- Protection class I, Pin temperature 70 °C,
- with V-Lock interlocking system
- Meets the Hospital Grade requirements of UL 817

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Technical Data

| | | | |
|---------------------------|---|-----------|---|
| Ratings UL/CSA | 13A / 125VAC; 50/60Hz | Connector | C13 IEC 60320-1 |
| Dielectric Strength | > 2 kVDC between L-N > 2 kVAC between L/N-PE (1 min/50Hz) | | UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 13A, Protection Class I |
| Allowable Operation Temp. | -25 °C to 70 °C | | |
| Degree of Protection | from front side IP 20 acc. to IEC 60529 | | |
| Protection Class | Suitable for appliances with protection class I acc. to IEC 61140 | | |
| Terminal | moulded | | |
| Material: Housing | PVC, Transparent | | |

Variants

| Connector | cable | | Plug | | | | | | | | Order Number | |
|-----------|--------|--------------|-------|------------|---------------|---------|-----------|-------------------------|----------|-------|--------------|-----------|
| Type | V-Lock | Cord Type | Color | Length [m] | Type | Country | Standard | Conductor cross section | Style | Index | | |
| C13 | ● | SJT 3x16 AWG | white | 3.0 | North America | USA | NEMA 5-15 | 3 x 16 AWG | straight | - | | 6051.2121 |

Packaging unit 40 Pcs**Passende Stecker verriegelt zu****Category / Description**[Appliance Inlet Overview complete](#)

| | |
|--|------|
| IEC Appliance Inlet C14, Snap-in Mounting, Solder, Quick-connect, Screw or PCB Terminal | 6010 |
| IEC Appliance Inlet C14, Screw-on Mounting, Front or Rear Side, Solder or Quick-connect or Screw-on Terminal | 6048 |
| IEC Appliance Inlet C14, Screw-on Mounting, Front Side, Solder or Quick-connect, PCB or Screw Terminal | 6061 |
| IEC Appliance Inlet C14, Screw-on Mounting, Front Side, Solder or Quick-connect or Screw Terminal | 6062 |
| IEC Appliance Inlet C14, insert Mounting, Solder or Quick-connect, PCB or Screw Terminal | 6170 |

[Appliance Inlet further types to VAC13KS](#)

...



[Power Entry Module Overview complete](#)

| | |
|--|------|
| IEC Appliance Inlet C14 with Fuseholder 2-pole | 4707 |
| IEC Appliance Inlet C14 with Circuit Breaker TA35 2-pole | 6135 |
| IEC Appliance Inlet C14 with Circuit Breaker TA45 | 6145 |
| IEC Appliance Inlet C14, with Line Switch 2-pole, Voltage Selector and Fuseholder 1or 2-pole | 6766 |
| IEC Appliance Inlet C14 with Line Switch 1- or 2-pole | DC11 |
| Power Entry Module further types to VAC13KS | ... |

[Power Entry Module with line filter Overview complete](#)



| | |
|--|------|
| IEC Appliance Inlet C14 or C18 with Filter, ECO design, Front- or Rear Side Mounting | 5120 |
| IEC Appliance Inlet C14 or C18 with Filter, high attenuation, ECO design, Front- or Rear Side Mounting | 5123 |
| IEC Appliance Inlet C20 with Filter, ECO design, front or rear side Mounting | 5130 |
| IEC Appliance Inlet C14 with Filter, Circuit Breaker TA45 | 5145 |
| IEC Appliance Inlet C14 with High Frequency Filter, X2Y Technology, ECO design, Front- or Rear Side Mounting | 5150 |
| Power Entry Module with line filter further types to VAC13KS | ... |