

Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN - 1051016

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker strip, Strip, white, labeled, Can be labeled with: Plotter, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm

The illustration shows the version ZB 6:UNBEDRUCKT

Product Features

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

Key commercial data

Packing unit	1 PCE
Minimum order quantity	10 PCE
Custom tariff number	39269097
Country of origin	GERMANY

Technical data

Dimensions

Width (a)	6 mm
-----------	------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	For labeling according to customer requirements, please select product 0824992
Color	white
Inflammability class according to UL 94	V2
Components	free from silicone and halogen
Material	PA
Printing direction	Printed horizontally
Printing	Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500

Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN - 1051016

Technical data

General

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410