

# DRANI 20\* SERIES

## FOR DC BACKUP SYSTEM

AC - DC DIN RAIL MOUNTABLE POWER SUPPLY  
INDUSTRIAL CONTROL EQUIPMENT



## FEATURES

- P.F.C. FUNCTION AVAILABLE
- INPUT VOLTAGE 115/230VAC AUTO SELECT
- SELV COMPONENTS DESIGN
- 3 YEARS WARRANTY




## SELECTION CHART

### DRAN I 20 - 24 A \*


Wattage | DC Backup System  
12 : 13.6V OUT / 24 : 27.2V OUT / 48 : 54.5V OUT | SCREW TERMINALS

## MODEL LIST

MODEL NO.	INPUT VOLTAGE	OUTPUT WATTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	EFF. (min.)	EFF. (typ.)
<b>Single Output Models</b>						
DRANI 20-12A*	115 / 230 VAC	120 WATTS	+ 13.6 VDC	8.8 A	82%	84%
DRANI 20-24A*	115 / 230 VAC	120 WATTS	+ 27.2 VDC	4.4 A	84%	86%
DRANI 20-48A*	115 / 230 VAC	120 WATTS	+ 54.5 VDC	2.2 A	85%	87%



DRANI 20\* Series For DC Backup System Application



DRANI 20\* Series For DC Backup System Application

### Note :

1. The suffix "\*" is part of the model number, which specifies the product is designed and pre-trim for low-cost DC backup power system with external Lead-Acid battery, Relay and Fuse.
2. The manufacturer is liable neither for the external components nor the damage to the power supply causing by external components.
3. The total consumption current including loading and battery charging current should not exceed the maximum rated current of power supply.
4. The operation concept of DC backup power system :
  - A. When AC power alive : The "Rdy" is close circuit to active the external Relay . The power supply feeds current into the external loads and charges through Relay to the external battery as well.
  - B. When AC power interrupted : The "Rdy" is remain close circuit to maintain the external Relay remain active, the external battery supply current to the external loads.
  - C. When Battery power low : The "Rdy" become open circuit and the external Relay become inactive to disconnect the battery from external loads.



## SPECIFICATION

All Specifications Typical At Nominal Line, Full Load, 25°C Unless Otherwise Noticed

GENERAL						
Characteristics	Conditions	min.	typ.	max.	unit	
Switching frequency	Vi nom, lo nom		55		KHz	
Isolation voltage	Input-Output	3,000 / 4,242			VAC / VDC	
	Input-FG	1,500 / 2,121			VAC / VDC	
	Output-FG	500 / 710			VAC / VDC	
Isolation resistance	Input-Output, @ 500VDC	100			MΩ	
Ambient temperature	Operating at Vi nom	-35		+ 71	°C	
Derating (see derating curve)	Vi nom, from +61°C to +71°C			2.5	% / °C	
Storage temperature	Non operational	-40		+ 85	°C	
		20		95	% RH	
Temperature coefficient	Vi nom, lo min			± 0.03	% / °C	
MTBF	Bellcore Issue 6 @40°C, GB	12V		440,000	Hours	
		24V		450,000	Hours	
		48V		482,000	Hours	
Altitude during operation	IEC 60068-2-13			4,850	m	
Dimension	Screw terminal type	L124.5 x W64 x D123.6			mm	
Cooling	Free air convection					
Installation position	Vertical ( other direction may derating using )					
Pollution degree		2				

INPUT SPECIFICATIONS						
Characteristics	Conditions	min.	typ.	max.	unit	
Rated input voltage	lo nom	115 / 230 (auto select)			VAC	
Absolute input max. range	Ta min ... Ta max, lo nom	AC in	90		132	VAC
		AC in	180		264	VAC
		DC in	210		375	VDC
Input current	Vi : 115 / 230 VAC, lo nom		2.2 / 0.83		A	
Rated input current	Vi : 90 / 180 VAC, lo nom			2.8 / 1.4	A	
Line frequency	Vi nom, lo nom	47		63	Hz	
Inrush current	Vi : 115 / 230 VAC , lo nom			24 / 48	A	
Power dissipation	Vi : 230 VAC, lo nom	12V		24	W	
		24V		20	W	
		48V		19	W	
Leakage current	Input-Output			0.25	mA	
	Input-FG			3.5	mA	
P.F.C. (Passive)	Vi : 230VAC, lo nom		0.7			

OUTPUT SPECIFICATIONS						
Characteristics	Conditions	min.	typ.	max.	unit	
Output voltage accuracy (Adjusted before shipment)	Vi nom, lo max			± 1	%	
Minimum load	Vi nom	0			%	
Line regulation	lo nom, Vi min ... Vi max			± 0.5	%	
Load regulation	Vi nom, lo min ... lo nom			± 1	%	
Voltage trim range	Vi nom, 0.8 lo nom	12V		11.4	14.5	VDC
		24V		22.5	28.5	VDC
		48V		45	55	VDC
Hold up time	Vi : 115 / 230 VAC , lo nom	25 / 30			ms	
Turn on time	Vi nom, lo nom			1,000	ms	
	Vi nom, lo nom → 12V model : with 7000 μF CAP 24V, 48V models : with 3500 μF CAP			1,500	ms	
Rise time	Vi nom, lo nom			150	ms	
	Vi nom, lo nom → 12V model : with 7000 μF CAP 24V, 48V models : with 3500 μF CAP			500	ms	
Fall time	Vi nom, lo nom			150	ms	
Transient recovery time	Vi nom, I ~ 0.5 lo nom			2	ms	



## SPECIFICATION

All Specifications Typical At Nominal Line, Full Load, 25°C Unless Otherwise Noticed

OUTPUT SPECIFICATIONS					
Characteristics	Conditions	min.	typ.	max.	unit
Ripple & noise	Vi nom, Io nom, BW = 20MHz			50	mV
Power back immunity	Vi nom, Io nom	12V	18		VDC
		24V	35		VDC
		48V	63		VDC
Capacitor load	Vi nom, Io nom	12V		7,000	μF
		24V, 48V		3,500	μF
DC ON indicator threshold at start up (Green LED)	Vi nom, Io nom	12V	10.4	11.4	VDC
		24V	21.2	22.2	VDC
		48V	42.8	43.8	VDC
DC LOW indicator threshold after start up (Red LED)	Vi nom, Io nom	12V	10.3	11.3	VDC
		24V	21.1	22.1	VDC
		48V	42.7	43.7	VDC

CONTROL AND PROTECTION					
Characteristics	Conditions	min.	typ.	max.	unit
Input fuse		T3.15A / 250 VAC internal			
Internal surge voltage protection	IEC 61000-4-5	Varistor			
Rated over load protection	Vi nom	105		125	%
Power Rdy	Rdy Close indicator threshold at start up	12V	10.4	11.4	VDC
		24V	21.2	22.2	VDC
		48V	42.8	43.8	VDC
Power Rdy	Rdy Open indicator threshold after start up	12V	10.3	11.3	VDC
		24V	21.1	22.1	VDC
		48V	42.7	43.7	VDC
	Electrical isolation	500			VDC
Over voltage protection	Contact rating at 60VDC			0.3	A
	Vi nom, 0.8 Io nom (Auto Recovery)	125		140	%
Output short circuit		Fold forward			
Degree of protection		IP20			


APPROVALS AND STANDARDS	
UL / cUL	UL 508 Listed UL 60950-1 Recognized ISA 12.12.01(Class I, Division 2, Groups A, B, C and D)
TUV	EN 60950-1
CE	EN 61000-6-3, EN 55022 Class B, EN 61000-3-2 Class D, EN 61000-3-3 EN 61000-6-2, EN 55024, EN 61000-4-2 Level 4, EN 61000-4-3 Level 3 EN 61000-4-4 Level 4, EN 61000-4-5 L-N Level 3, L / N-FG Level 4 EN 61000-4-6 Level 3, EN 61000-4-8 Level 4, EN 61000-4-11 ENV 50204 Level 2, EN 61204-3
CCC	GB4943.1, GB9254, GB17625.1
Vibration resistance	meet IEC 60068-2-6 (Mounting by rail : 10-500 Hz, 2G, along X, Y, Z each Axis, 60 min for each Axis )
Shock resistance	meet IEC 60068-2-27 (15G, 11ms, 3 Axis, 6 Faces, 3 times for each Face)

## PHYSICAL CHARACTERISTICS

Case size	124.5 x 64 x 123.6 mm (4.9x 2.52 x 4.87 inches)
Case material	Metal
Weight	920 g
Packing	1.02 kg ; 20pcs / 21.5 kg / 2.01 CUFT

## MECHANISM & PIN CONFIGURATION

mm [inch]



### CONSTRUCTION

Easy snap-on mounting onto the DIN-Rail (TS35/7.5 or TS35/15), unit sits safely and firmly on the rail.

### INSTALLATION

Ventilation / Cooling  
Normal convection  
All sides 25mm free space  
For cooling recommended  
Connector size range  
Screw terminal:  
AWG24-10(0.2~4mm<sup>2</sup>) flexible / solid cable,  
-Input connector can withstand torque at maximum 9 pound-inches.  
-Output connector can withstand torque at maximum 5.5 pound-inches.  
8 m/m stripping at cable end recommends  
Use copper conductors only, 60 / 75°C

#### GENERAL TOLERANCE


0.00[0.00] - 30.00[1.18]	±0.30[0.01]
30.00[1.18] - 120.00[4.72]	±0.50[0.02]
120.00[4.72] - 400.00[15.75]	±0.80[0.03]

## PIN ASSIGNMENT

PIN NO.	Designation	Description
1, 2	OUT	RDY
3, 4		V +
5, 6		V -
7	IN	⊕
8		L
9	N	
	OTHER	DC ON
		DC LO
		Vout ADJ.

## CIRCUIT SCHEMATIC

• Block diagram for DRAN120\* series



## DERATING CURVE

