

EVOLite®

MICROPEAK - SLIP RATCHET - VENTILATED

PRODUCT CODE: AJD160-00_-00

THE LIGHTEST SAFETY HELMET AVAILABLE IN EUROPE

TECHNICAL SPECIFICATION

HEAD PROTECTION

INSTRUCTIONS FOR USE

Fit helmet on head and fasten strap to ensure fit

For adequate protection this helmet must be worn with peak facing forward

Ensure the helmet is adjusted to the size of the user's head



SHELL:

High strength engineering grade ABS which has been UV Stabilised




WEBBING HARNESS:

HDPE Strap & Webbing Clips with Polyester Webbing Straps



CHAMLON™ SWEATBAND:

Egyptian cotton core with porous PU coating for maximum sweat absorption. PH neutral, dermatologically tested



SLIP RATCHET:

One Touch™ Slip Ratchet version of the EVOLite® is so simple to fit that it can be adjusted with just one finger



CLEANING & MAINTENANCE

The unit may be cleaned with soap and warm water and dried with a soft cloth

The helmet should not be cleaned with chemical or abrasive cleaners

The helmet should be stored out of direct sunlight

The helmet should be stored away from chemicals and extremes of temperature

CONFORMITY

EN 397 & GOCT P 50460-92 for Industrial Safety Helmets

EN 50365 for Helmets for use in low voltage installations

EC Certificate Number 0279, issued by BSi Product Certification

Meets optional Lateral Deformation performance

Wide size range. Slip or wheel ratchet - High comfort fit

Available vented. Available with mid or micro peak

Company personalisation available by printing



MANUFACTURING FOR SAFETY
WWW.JSP.CO.UK

UKSALES@JSP.CO.UK
TEL: +44 (0)1993 826050



EVOLite®

MICROPEAK - SLIP RATCHET - VENTILATED

PRODUCT CODE: AJD160-00_- _00

THE LIGHTEST SAFETY HELMET AVAILABLE IN EUROPE

TECHNICAL SPECIFICATION

HEAD PROTECTION



DIMENSIONS OF OUTER PACKAGING

Quantity: 10

Weight: 3.2kg (Approx.)

HEIGHT:
450mm



WIDTH:
240mm

LENGTH:
580mm

HELMET FEATURES

EN STANDARD	EN397 EN50365	Yes Yes
PERFORMANCE	Impact Resistance Lateral Deformation Electrical Insulation	Yes 50 Joules Yes EN50365 1000V
TEMPERATURE RESISTANCE	+50°C Low Temperature	Yes Yes: EN397 -30°C ГОСТ P 50460-92 -30°C
SHELL MATERIAL	ABS Recyclable UV Stabilised	Yes Yes Yes
HARNES MATERIAL	HDPE Textile	Yes Yes
OPTIONS	Universal Accessories Reflective CR2 option Integrated Eyewear Micro Peak	Yes Yes Yes Yes
HARNES SYSTEM OPTIONS	JSP 3D Slip Ratchet 6 pts	Yes Yes Yes
CHINSTRAP OPTIONS	4 pts 2 pts	Yes Yes
LOGO OPTIONS	Front Rear Side MOQ Logo Individual Name	Yes Yes Yes 10 Yes

DIMENSIONS OF HELMET

Size: 530 - 640mm

Weight: 299g (Approx.)



HELMET COLOURS

Insert the following two digit number in place of the dashes in the product code of your desired helmet



01 White 02 Yellow 05 Blue 06 Red

LIMITATIONS OF USE

Protection will only be offered if the helmet is fitted correctly

Any helmet subjected to severe impact should be replaced immediately. Do not apply paint, solvents or adhesive labels except in accordance with instructions from the manufacturer

The harness, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area, remove the helmet and seek medical advice

The attention of users is also drawn to the dangers of modifying or removing any of the original component parts, other than as recommended by the manufacturer



MANUFACTURING FOR SAFETY
WWW.JSP.CO.UK



UKSALES@JSP.CO.UK
TEL: +44 (0)1993 826050



Issued 15/08/13, V4