

**KEMET Part Number: C0603C104K5RACAUTO**  
(C0603C104K5RACAUTO7867)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Automotive Grade, 0.1 uF, +/-10% Tol, 50V, X7R, 0603



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.60	+/-0.15
W	0.80	+/-0.15
T	0.80	+/-0.07
B	0.35	+/-0.15
S	0.7	MIN

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Type:	Paper Tape
Package Quantity:	4000

General Information	
Supplier:	KEMET
Part Type Description:	SMD, MLCC, Temperature Stable, Automotive Grade
Miscellaneous Electrical:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications	
Capacitance:	0.1 uF
Chip Size:	0603
Voltage:	50V
Temperature Coefficient:	X7R
Tolerance:	+/-10%
Application:	Automotive/Standard Chip
Termination Type:	Tin
Marked:	No
Temperature Range:	-55/+125C
Dissipation Factor:	2.5%
Insulation Resistance:	5 GOhm
Dielectric Strength:	125V