



RST-RKWT/LED**RST-RKWT/LED**

Diagram of a 4-wire cable with the following color coding and terminal labels:

- 1: braun/brown (+)
- 2: weiß/white
- 4: schwarz/black
- 3: blau/blue (-)

The diagram also shows the following terminal labels and their corresponding conductors:

- ge (green) connected to conductor 2 (white)
- rt (red) connected to conductor 4 (black)
- gn (green) connected to conductor 3 (blue)



Be Certain with Belden

M12-Round-Plug Connector, Double-Ended Cordsets, According to IEC 61076-2-101

RST-RKWT/LED

Technical Data

Environmental

Degree of protection IP 67 / NEMA 6P
Operating temperature range -25°C (-13°F) / +80°C (+176°F)

Mechanical

Housing / Molded body TPU
Insert TPU
Contact RST: CuSn, pre-nickel and 0.8 microns gold-plated
RKWT/LED: CuSn, pre-nickel and 0.3 microns gold-plated
Coupling nut CuZn, nickel-plated
O-ring FKM (only RKWT/LED)

Electrical

Nominal current at 40°C 4 A
Nominal voltage 10–30 V DC
Rated voltage 32 V
Insulation resistance > 10⁹ Ω
Pollution degree 3

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Jacket Color	OD
224	PUR, halogen-free	3 x 0.34 mm ²	Black	.169" (4.3 mm)
225	PUR, halogen-free	4 x 0.34 mm ²	Black	.185" (4.7 mm)
251	PUR, halogen-free welding spark proof	4 x 0.34 mm ²	Orange	.185" (4.7 mm)
260	PUR, halogen-free welding spark proof	3 x 0.34 mm ²	Orange	.177" (4.5 mm)

Part Number	Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RST 3-RKWT/LED A 4-3-224/...M	3	PUR, halogen-free	0.3 M / 0.6 M / 1 M / 1.5 M / 2 M / 5 M	   
RST 3-RKWT/LED A 4-3-260/...M		PUR, halogen-free	0.3 M / 0.6 M / 1 M / 1.5 M / 2 M / 5 M	    
RST 4-RKWT/LED P 4-225/...M	4	PUR, halogen-free, weld spark proof	0.3 M / 0.6 M / 1 M / 1.5 M / 2 M / 5 M	   
RST 4-RKWT/LED P 4-251/...M		PUR, halogen-free	0.3 M / 0.6 M / 1 M / 1.5 M / 2 M / 5 M	    
RST 4-RKWT/LED R 4-251/...M	4	PUR, halogen-free, weld spark proof	0.3 M / 0.6 M / 1 M / 1.5 M / 2 M / 5 M	    