



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™

CRIMPER WIRE-FERRULE 20-10 AWG

Wire Ferrule Crimper



Image
Unavailable

Cat No: PA1647

UPC No: 769328103823

Description

- Professional-quality crimping tool for insulated and non-insulated wire ferrules with arange of 20-10 AWG (0.5-6.0 mm²)
- Ferrules conform to DIN 46228 Pt. 1 and 4
- Ferrule insertion from the side of the tool
- Single tool for entire wire range (no additional dies are required)
- Durable steel construction for long life
- Ergonomic handles for low-effort operation

Specifications

- Application : For Insulated And Non-Insulated Wire Ferrules With A Range Of 20-10 AWG (0.500 - 6.000 SQ-MM)
- Crimping Range : 20-10 AWG
- Handle Type : Ergonomic
- Material : Durable Steel
- Replacement Part : PA2681 Replacement die set
- Standard : DIN
- Type : Wire Ferrule
- Weight : 15.200 OZ (430.000 GM)