


KEMET Part Number: C315C479D2G5TA
(C315C479D2G5TA)

Capacitor, ceramic, 4.7 pF, +/-0.5pF Tol, 200V, C0G, Lead Spacing=0.1"



Dimensions (in)

| Symbol | Dimension | Tolerance |
|--------|-----------|---------------|
| L | 0.15 | MAX |
| H | 0.21 | MAX |
| T | 0.1 | MAX |
| S | 0.1 | +/-0.03 |
| LL | 0.276 | MIN |
| F | 0.02 | +0.004/-0.001 |
| K | 0.02 | |

Notes:

- Voltage code from part number
- EIA capacity code

General Information

| | |
|-----------|-------|
| Supplier: | KEMET |
|-----------|-------|

Specifications

| | |
|--------------------------|---------------------------|
| Capacitance: | 4.7 pF |
| Lead Spacing: | 0.1" |
| Voltage: | 200V |
| Temperature Coefficient: | C0G |
| Tolerance: | +/-0.5pF |
| Application: | Commercial Standard |
| Temperature Range: | -55/+125C |
| Body Type: | Radial Conformal (Dipped) |
| Lead Type: | Standard Leads |
| Lead Form: | Straight |
| Termination Type: | Tin |

Packaging Specifications

| | |
|-------------------|------|
| Package Kind: | Bulk |
| Package Type: | Bag |
| Package Quantity: | 500 |