

**Passeinsatz für Einsätze E14 4 A
DIGI CHECK PRO**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

Type	DIGI CHECK PRO
Order No.	9918870000
Version	2-pole voltage tester type 1152
GTIN (EAN)	4032248405756
Qty.	1 pc(s).

Passeinsatz für Einsätze E14 4 A DIGI CHECK PRO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Weight	290 g	Net weight	290 g
--------	-------	------------	-------

Product data

Rated voltage, min.	0.30 V	AC voltage measuring range	5-690 V
Frequency range, min.	0 Hz	Frequency range, max.	100 Hz
Rated voltage, max.	690 V AC/DC	Protection degree	IP 65
Battery type	1.5 V type AAA battery	Tested and approved according to	EN/IEC 61243-3 :2010-10 (VDE 0682 Part 401)
Input resistance, voltage	On operating the double switch $\geq 300 \text{ k}\Omega$	Peak voltage resistance	8 kV
Display	LCD		

Classifications

ETIM 2.0	EC000494	ETIM 3.0	EC000494
UNSPSC	41-11-36-37	eClass 4.1	27-20-03-08
eClass 5.1	27-20-03-08	eClass 6.2	27-20-03-08
eClass 7.1	27-20-03-08		

Product information

Descriptive text ordering data	Protective case included
Description of article	Voltage tester up to 690 V/ 100 Hz LCD
Product description	<ul style="list-style-type: none"> • Test probe illumination • Selectable load for residual current test • Phase sequence indicator

Approvals

Approvals



ROHS	Conform
------	---------

**Passeinsatz für Einsätze E14 4 A
DIGI CHECK PRO**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

