



ANSI Standard In-Line Thermocouple Sockets



'Accepts standard round plug pins'

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors


Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Standard in-line thermocouple socket with connections to suit thermocouple type being used
- Accepts standard round plug pins
- Suitable for industrial applications
- Available in Thermocouple types K, J, T
- For Types K, J, T contacts are made from true Thermocouple alloys
- Contacts are polarised to prevent incorrect connection
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (ANSI)	+Positive (alloy type)	-Negative (alloy type)	Labfacility Code	Farnell Code
K	Yellow	+Nickel Chromium	-Nickel Alloy	AS-K-F	234-7147
J	Black	+Iron	-Copper Nickel	AS-J-F	234-7146
T	Blue	+Copper	-Copper Nickel	AS-T-F	234-7148



FAR040/0613 ANSI Standard In-Line Thermocouple Sockets

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com