


KEMET Part Number: C320C153K5R5TA
(C320C153K5R5TA)

Capacitor, ceramic, 0.015 uF, +/-10% Tol, 50V, X7R, Lead Spacing=0.1"



Dimensions (in)

Symbol	Dimension	Tolerance
L	0.2	MAX
H	0.26	MAX
T	0.125	MAX
S	0.1	+/-0.03
LL	0.276	MIN
F	0.02	+0.004/-0.001
K	0.02	

Notes:

- Voltage code from part number
- EIA capacity code

General Information

Supplier:	KEMET
-----------	-------

Specifications

Capacitance:	0.015 uF
Lead Spacing:	0.1"
Voltage:	50V
Temperature Coefficient:	X7R
Tolerance:	+/-10%
Application:	Commercial Standard
Temperature Range:	-55/+125C
Body Type:	Radial Conformal (Dipped)
Lead Type:	pcleads
Lead Form:	Straight
Termination Type:	Tin (Sn)

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500