

**KEMET Part Number: C322C102F5G5TA**  
(C322C102F5G5TA)

Capacitor, ceramic, 1000 pF, +/-1% Tol, 50V, COG, Lead Spacing=0.2"



Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.2	MAX
H	0.26	MAX
T	0.125	MAX
S	0.2	+/-0.03
LL	0.276	MIN
F	0.02	+0.004/-0.001
K	0.02	
G	0.031	REF

Notes:  
-Voltage code from part number  
-EIA capacity code

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	1000 pF
Lead Spacing:	0.2"
Voltage:	50V
Temperature Coefficient:	COG
Tolerance:	+/-1%
Application:	Commercial Standard
Temperature Range:	-55/+125C
Body Type:	Radial Conformal (Dipped)
Lead Type:	Standard Leads
Lead Form:	Hockey Stick
Termination Type:	Tin (Sn)

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500