


**KEMET Part Number: C330C104MCR5TA**  
(C330C104MCR5TA)

Capacitor, ceramic, 0.1 uF, +/-20% Tol, 500V, X7R, Lead Spacing=0.2"



**Dimensions (in)**

Symbol	Dimension	Tolerance
L	0.3	MAX
H	0.36	MAX
T	0.25	MAX
S	0.2	+/-0.03
LL	0.276	MIN
F	0.02	+0.004/-0.001
K	0.02	

Notes:

-Voltage code from part number

-TC/Dielectric code from part number

**General Information**

Supplier:	KEMET
-----------	-------

**Specifications**

Capacitance:	0.1 uF
Lead Spacing:	0.2"
Voltage:	500V
Temperature Coefficient:	X7R
Tolerance:	+/-20%
Application:	Commercial High Voltage
Temperature Range:	-55/+125C
Body Type:	Radial Conformal (Dipped)
Lead Type:	Standard Leads
Lead Form:	Straight
Termination Type:	Tin (Sn)

**Packaging Specifications**

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	250