

## M96915 Fiber - Tight Buffer Interconnect Cables - Riser (OFNR)



For more Information  
please call

1-800-Belden1



### Description:

Interconnect Cables are designed for low fiber-count premises environments. They are small and very flexible, making them ideal for confined spaces. Their aesthetic appearance makes these cables suitable for use in open office environments.

### Physical Characteristics (Overall)

Fiber Type:	62.5/125/900 Micron
Number of Fibers:	2
Core Diameter:	62.5 +/- 2.5
Core Non-Circularity:	5% Maximum
Clad Diameter:	125 +/- 2
Clad Non-Circularity:	2% Maximum
Primary Coating Material:	Acrylate
Primary Coating Diameter:	245 +/- 10
Secondary Coating Material:	Engineering Thermoplastic
Secondary Coating Diameter:	900 +/- 50

#### Fiber Color Code Chart:

Color
Blue
White

Core-clad Offset:	3 Microns Maximum
-------------------	-------------------

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Color:	Orange
---------------------	--------

#### Strength Member

Strength Member Material:	Aramid Yarn
---------------------------	-------------

#### Overall Cabling

Overall Nominal Diameter:	2.896 x 5.842 mm
---------------------------	------------------

### Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-20°C To +70°C
Bulk Cable Weight:	16.073 Kg/Km
Min. Bend Radius (Install)/Minor Axis:	43.180 mm
Min. Bend Radius for Long Term Application:	27.940 mm
Max. Load for Installation:	800.676 N

## M96915 Fiber - Tight Buffer Interconnect Cables - Riser (OFNR)

Max. Load for Long Term Application:	311.374 N
Proof Test:	100 kpsi

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	OFNR
CEC/C(UL) Specification:	OFN
IEEE Specification:	802.3Z
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Flame Test

C(UL) Flame Test:	FT4
-------------------	-----

#### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No

### Optical Characteristics (Overall)

Maximum Attenuation @ 850nm:	3.5 dB/km
Maximum Attenuation @ 1300nm:	1.25 dB/km
Point Loss @ 850nm & 1300nm:	.2
Minimum Bandwidth @ 850nm:	200 MHz*km
Minimum Bandwidth @ 1300nm:	500 MHz*km
Refractive Index @ 850nm:	1.496
Refractive Index @ 1300nm:	1.491
Numerical Aperature:	.275
Maximum Gigabit Ethernet Length @ 850nm:	300
Maximum Gigabit Ethernet Length @ 1300nm:	550

### Reference (Overall)

Previous Part Number:	PTZ6002
-----------------------	---------

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 3    Revision Date: 08-26-2008

© 2010 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract,

---

## M96915 Fiber - Tight Buffer Interconnect Cables - Riser (OFNR)

negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.