

For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, twisted pairs, individually Beldfoil® shielded (100% coverage) each with 24 AWG stranded tinned copper drain wire, overall PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

| # Pairs | AWG | Stranding | Conductor Material | Dia. (mm) |
|---------|-----|-----------|--------------------|-----------|
| 4 | 24 | 7x32 | TC - Tinned Copper | 0.6096 |

Total Number of Conductors: 8

Insulation

Insulation Material:

| Insulation Trade Name | Insulation Material | Wall Thickness (mm) |
|-----------------------|-------------------------|---------------------|
| Datalene® | FPE - Foam Polyethylene | 0.483 |

Inner Shield

Inner Shield Material:

| Inner Shield Trade Name | Type | Inner Shield Material | Coverage (%) |
|-------------------------|------|------------------------------|--------------|
| Beldfoil® (Z-Fold®) | Tape | Aluminum Foil-Polyester Tape | 100 |

Inner Shield Drain Wire AWG:

| AWG |
|-----|
| 24 |

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material | Nom. Wall Thickness (mm) |
|--------------------------|--------------------------|
| PVC - Polyvinyl Chloride | 1.219 |

Overall Cable

Overall Nominal Diameter: 9.220 mm

Pair

Pair Color Code Chart:

| Number | Color |
|--------|---------------|
| 1 | Black & Red |
| 2 | Black & White |
| 3 | Black & Green |
| 4 | Black & Blue |

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 60°C (UL AWM Style 2493)

Bulk Cable Weight: 75.898 Kg/Km

Max. Recommended Pulling Tension: 289.133 N

Min. Bend Radius/Minor Axis: 95.250 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

| | |
|---------------------------------------|----------------------------|
| NEC/(UL) Specification: | CM |
| CEC/C(UL) Specification: | CM |
| AWM Specification: | UL Style 2493 (300 V 60°C) |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 01/01/2004 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |

Flame Test

UL Flame Test: UL1685 UL Loading

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 89728

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

100

Nom. Inductance:

Inductance (µH/m)

0.75463

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

41.0125

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

76.1192

Nominal Velocity of Propagation:

VP (%)

76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

78.744

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 49.215 Ohm/km

Nom. Attenuation:

| Freq. (MHz) | Attenuation (dB/100m) |
|-------------|-----------------------|
| .384 | 2.42794 |
| .7056 | 2.85447 |
| .768 | 2.88728 |
| 1.024 | 3.08414 |

| | |
|---------|---------|
| 1.4112 | 3.31381 |
| 1.536 | 3.37943 |
| 2.048 | 3.70753 |
| 2.8224 | 4.23249 |
| 3.072 | 4.42935 |
| 4.096 | 5.15117 |
| 5.6448 | 5.84018 |
| 6.144 | 6.03704 |
| 8.192 | 6.98853 |
| 11.2896 | 8.03845 |
| 12.288 | 8.43217 |
| 24.576 | 11.7132 |

Max. Operating Voltage - UL:

| Voltage | Description |
|-----------|-------------------|
| 300 V RMS | UL AWM Style 2493 |

Max. Recommended Current:

| Current |
|-------------------------------|
| 2.5 Amps per conductor @ 25°C |

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|--------------|----------|-------------|--------|-------|-----------------------|
| 9728 060100 | 30 MT | 2.722 KG | CHROME | | 4 FS PR #24 FHDPE PVC |
| 9728 0601000 | 305 MT | 24.948 KG | CHROME | C | 4 FS PR #24 FHDPE PVC |
| 9728 060500 | 152 MT | 13.154 KG | CHROME | | 4 FS PR #24 FHDPE PVC |
| 9728 0605000 | 1,524 MT | 133.810 KG | CHROME | | 4 FS PR #24 FHDPE PVC |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-15-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.