



For more Information  
please call

1-800-Belden1



## General Description:

RG-8X type, 15 AWG solid .057" bare copper conductor, gas-injected foam HDPE insulation, Duobond® II + tinned copper braid shield (95% coverage), PVC jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	15	Solid	BC - Bare Copper	1.4478

Total Number of Conductors: 1

### Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	3.81

### Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

### Overall Cable

Overall Nominal Diameter: 6.096 mm

## Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

UL Temperature Rating: 60°C

Bulk Cable Weight: 59.528 Kg/Km

Max. Recommended Pulling Tension: 329.167 N

Min. Bend Radius/Minor Axis: 63.500 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 8/X

### Flame Test

UL Flame Test: UL1666 Vertical Shaft

CSA Flame Test: FT4

### Suitability

Suitability - Indoor: Yes

### Plenum/Non-Plenum

Plenum (Y/N): No

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)

50

### Nom. Inductance:

Inductance (µH/m)

0.19686

### Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

75.463

### Nominal Velocity of Propagation:

VP (%)

86

### Nominal Delay:

Delay (ns/m)

3.87158

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

10.4992

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

9.1868

### Maximum VSWR:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Max. VSWR
		5	6000	1.25:1

### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
5.000	1.903
10.000	2.526
30.000	4.265
50.000	5.250
150.000	9.187
220.000	11.155
450.000	16.077
900.000	22.967
1500.000	29.857
1800.000	33.138
2000.000	35.107

2500.000	39.372
3000.000	43.965
3500.000	47.903
4500.000	54.793
5800.000	63.980
6000.000	64.964

**Max. Power Rating:**

Freq. (MHz)	Rating (W)
30	1526
50	1186
150	673
220	556
450	382
900	286
1500	205
1800	187
2000	177
2500	156
3000	143
3500	132
4500	116
5800	102
6000	100

**Max. Operating Voltage - UL:**

Voltage
300 V RMS

**Sweep Test**

**Sweep Testing:** 100% Sweep tested to 6 GHz.

**Misc. Information (Overall)**

**Notes (Overall)**

**Notes:** Belden® The Wire in Wireless®

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7808R 0101000	305 MT	19.958 KG	BLACK	C	RF240 WIRELESS 50OHM COAXFRPVC
7808R 010500	152 MT	9.752 KG	BLACK	C	RF240 WIRELESS 50OHM COAXFRPVC

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 6    Revision Date: 07-19-2013

© 2013 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

