


For more Information
please call

1-800-Belden1



General Description:

23 AWG stranded (7x32) .023" bare compacted copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), polyethylene jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	23	7x32	BCC - Bare Compacted Copper	0.5842

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PE - Polyethylene	3.7084

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PE - Polyethylene

Overall Cable

Overall Nominal Diameter: 5.588 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 38.693 Kg/Km

Max. Recommended Pulling Tension: 200.169 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	Mini 59/U

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - When supported by a messenger wire
Suitability - Burial:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.387158

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

68.901

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/m)

5.05274

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

62.6671

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

14.7645

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	1.3124
3.6	1.9686
10.0	3.9372
71.5	10.8273
135	15.4207
270	22.3108
360	26.248
540	32.4819
720	38.0596
750	39.0439
1000	45.2778

Max. Operating Voltage - Non-UL:

Voltage

2300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

Other Electrical Characteristic 2:

Return Loss tested in accordance with ASTM D-4566 paragraph 45.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	216.000	27.000
216.000	850.000	21.000

Sweep Test

Sweep Testing:

100% Sweep tested 5MHz to 850MHz.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8279 0101000	305 MT	10.433 KG	BLACK	C	MINI VIDEO CABLE
8279 010500	152 MT	5.216 KG	BLACK		MINI VIDEO CABLE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 09-30-2009

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.