

For more Information
please call

1-800-Belden1



General Description:

16 AWG stranded (19x29) tinned copper conductors, PVC insulation, twisted pair, tinned copper spiral wrapped shield (85% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
1	16	19x29	TC - Tinned Copper	1.4986

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PVC - Polyvinyl Chloride	2.667

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Spiral Serve	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 7.112 mm

Pair

Pair Color Code Chart:

Color
Black and White

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C
Bulk Cable Weight:	62.504 Kg/Km
Max. Recommended Pulling Tension:	271.340 N
Min. Bend Radius/Minor Axis:	76.200 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

CSA Flame Test:	FT4
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

37

Nom. Inductance:

Inductance (µH/m)

0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

187.017

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

321.538

Nominal Velocity of Propagation:

VP (%)

65

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

15.5848

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

62.339

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

7.1 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8780 060U1000	305 MT	19.958 KG	CHROME		1 PR #16 PVC SHLD PVC
8780 0601000	305 MT	20.865 KG	CHROME	C	1 PR #16 PVC SHLD PVC
8780 060500	152 MT	10.433 KG	CHROME	C	1 PR #16 PVC SHLD PVC
8780 0605000	1,524 MT	102.059 KG	CHROME		1 PR #16 PVC SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 10-15-2012

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.