

# HB04UC

## 4.0W Unregulated High Isolation DC/DC Converter



#### **FEATURES**

RoHS compliant
----------------

- High Isolation 3000v Rating
- 8000v Isolation Test Voltage
- Barrier 100% Production Tested
- Low Barrier Capacitance 10pf
- Low Leakage Current 2ma Max
- Internal Filtering

#### **Applications**

Biomedical Data Acquisition
Industrial Process Control
Analytical Measurements
Ground Loop Elimination
Intrinsic Safety Systems

### **PRODUCT OVERVIEW**

The HB04UC Series is a low-cost, high-isolation voltage, unregulated, single and dual output DC/DC converter. The dielectric withstand characteristics of each converter is tested in production to ensure barrier integrity.

The HB04UC Series uses advanced circuit design and packaging technology to realize superior reliability and performance. A 100kHz driven push-pull oscillator is used to ensure stable frequency and non-saturating operation of the input stage. This means there are no high peak voltages or currents like other design topologies, which can reduce unit reliability. Reduced parts count adds to the reliability of the HB04UC Series.

The high efficiency of the HB04UC Series means less internal power dissipation. With less heat to dissipate, the HB04UC Series can operate over a wider ambient temperature range with no degradation of reliable operation.

The HB04UC Series offers the user low cost without sacrificing reliability. The use of surface mounted devices and manufacturing technologies make it possible to offer premium performance at low cost.

# MECHANICAL



# muRata Ps Murata Power Solutions

# 4.0W Unregulated High Isolation DC/DC Converter

**HB04UC** 

### **ELECTRICAL SPECIFICATIONS**

Specifications typical at T<sub>A</sub> = +25°C, nominal input voltage, rated output current unless otherwise noted.

				INPUT CURRENT		
MODEL	VOLTAGE	VOLTAGE	CURRENT	NO LOAD	RATED LOAD	EFFICIENCY
	(VDC)	(VDc)	(mA)	(mA)	(mA)	(%)
HB04U05S05QC HB04U05S12QC HB04U05S15QC	5 5 5	5 12 15	800 333 267	60 60 60	1000 1000 1000	80 
HB04U12S05QC	12	5	800	25	380	87
HB04U12S12QC	12	12	333	25	380	87
HB04U12S15QC	12	15	267	25	380	87
HB04U15S05QC	<del>15</del>	5	800	<del>20</del>	<del>310</del>	<del>87</del>
HB04U15S12QC	15	12	333	20	310	87
HB04U15S15QC	15	15	267	20	310	87
HB04U05D05QC	5	±5	±400	60	944	85
HB04U05D12QC	5	±12	±167	60	944	85
HB04U05D15QC	5	±15	±134	60	944	85
HB04U12D05QC HB04U12D12QC HB04U12D15QC	12 12 12	±5 <u>±12</u> ±15	±400 ±167 ±134	25 25 25	375 <del>375</del> 375	88 
HB04U15D05QC	15	±5	±400	20	<del>300</del>	88
HB04U15D12QC	15	±12	±167	20	300	88
HB04U15D15QC	15	±15	±134	20	300	88

Note: Other input to output voltage options may be available. Please consult factory. Models with strikethrough have been discontinued.

### **COMMON SPECIFICATIONS**

Specifications typical at TA = +25°C, nominal input voltage, rated output current unless otherwise noted.

PARAMETER	CONDITIONS	MIN	ТҮР	MAX	UNITS
INPUT					
Voltage Range		4.5	5	5.5	VDC
		10.8	12	13.2	
		13.5	15	16.5	
Reflected Ripple Current			35 <sup>1</sup>		mAp-p
ISOLATION					
Rated Voltage		3000			VDC
Test Voltage	60 Hz, 10 Seconds	8000			Vpk
Resistance			10		GΩ
Capacitance			10		pF
Leakage Current	VISO= 240VAC, 60Hz		1.2	2	µArms
OUTPUT					
Rated Power			4		W
Voltage Setpoint Accuracy			±3	±5	%
Temperature Coefficient			±0.02		%/°C
Ripple & Noise	BW = DC to 10MHz		100		mVp-p
BW = 10Hz to $2MHz$			20		mVrms
Line Regulation	High Line to Low Line		±1.5		%/% Vin
Load Regulation	See performance curves				
GENERAL					
Switching Frequency			100		kHz
Package Weight			22		g
MTTF per MIL-HDBK-217, Rev. E	Circuit Stress Method				
Ground Benign	$T_A = +25^{\circ}C$		200,000		Hr
Constitution		25		170	°C
		-25		+70	°C
Storage		-40		+110	$\tilde{\mathfrak{O}}$
otorago		10		0	÷

1. Reflected ripple current is measured at 50% load with a 33uF capacitor across the input of the UUT.



HB04UC

# THROUGH-HOLE SOLDERING INFORMATION

These devices are intended for wave soldering or manual soldering. They are not intended to be subject to surface mount processes under any circumstances.

The normal wave soldering process can be used with these devices where the device is subjected to a maximum wave temperature of 260°C for a period of no more than 10 seconds. Within this time and temperature range, the integrity of the device's plastic body will not be compromised and internal temperatures within the converter will not exceed 175°C. Care should be taken to control manual soldering limits identical to that of wave soldering.

### **ABSOLUTE MAXIMUM RATINGS**

Internal Power Dissipation	1W
Short Circuit Duration	Momentary
Lead Temperature (soldering, 10 seconds max)	+300°C

### **ORDERING INFORMATION**



## **TYPICAL PERFORMANCE CURVES**





4.0W Unregulated High Isolation DC/DC Converter

**HB04UC** 

Murata Power Solutions, Inc. 11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A. ISO 9001 and 14001 REGISTERED



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>: Refer to: <u>http://www.murata-ps.com/requirements/</u>

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.