

Delivery Program

Product Category:	Load Cells
Model:	13 Subminiature
Order Code(s):	AL322

USE THE CHART BELOW TO DETERMINE LEAD TIMES¹

The range or option code with the longest lead time dictates the shipping time. Categories shaded in grey are required selections. For example (reference only):

If you build this:	The order configuration is this:	The delivery class is:
AL322 + 1000 g load range (AR), 60 °F to 160 °F (1a), Unamplified, mV/V output (2u), and 5 ft integrated cable with balance board	AL322 – AR – 1a – 2u	Quick ship, ships in 1 to 5 days
AL322 +1000 g load range (AR), 60 °F to 160 °F (1a), Unamplified, mV/V output (2u), and Phoenix connect on end of cable (6v)	AL322 – AR – 1a – 2u – 6v	Fast-track manufacture, ships within 4 weeks
AL322 +500 g (AP), 30 °F to 130 °F (1b), Unamplified, mV/V output (2u), and Connector on end of cable (15d)	AL322 – AP – 1b – 2u – 15d	Build-to-order, call Honeywell for lead time

	Quick-ship (Ships in 1-5 days)	Fast track manufacture (Ships within 4 weeks)	Build-to-order (Call Honeywell 1-800-848-6564 or +1 614-850-5000)
Load range	1000 g (AR); 10 (AV), 25 (BL), 50 (BN), 100 (BR), 250 (CN), 500 (CR), 1000 (CV) lb		150 (AL), 250 (AN), 500 (AP) g; 5 (AT)lb
Temperature compensation	1a. 60 °F to 160 °F *	1b. 30 °F to 130 °F 1c. 0 °F to 185 °F 1d. -20 °F to 200 °F 1e. -20 °F to 200 °F 1j. 0 °C to 50 °C 1k. -20 °C to 85 °C 1m. -25 ° to 110 °C	
Internal amplifiers	2u. Unamplified, mV/V output *		
Electrical termination	5 ft integral cable with balance board *	6v. Phoenix connector on end of cable	15d. Connector on end of cable
Overload stops			4a. Overload stops
Special calibration		9a. 10 point (5 up/5 down) 20 % increments @ 68 °F 9b. 20 point (10 up/10 down) 10 % increments @ 68 °F	
Shock and vibration			44a. Shock and vibration resistance

¹ LEAD/SHIPPING TIMES ARE APPROXIMATIONS AND MAY VARY DEPENDING ON PRODUCT AVAILABILITY AND OTHER FACTORS. IN NO EVENT SHALL HONEYWELL BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, CONSEQUENTIAL, EXEMPLARY, OR PUNITIVE DAMAGES, EVEN WHERE HONEYWELL HAS BEEN ADVISED OF, OR IS OTHERWISE AWARE OF, THE POSSIBILITY OF SUCH DAMAGES, FOR FAILURE TO MEET SUCH LEAD / SHIPPING TIMES.

* Default options.

Note: Before selecting option/s, please refer to the Test and Measurement catalog or product data sheet for special application notes and compatibility. A catalog can be ordered on-line at <https://home.honeywell-online.com/newTMCatalog>. Product data sheets are available on Honeywell's web site at <http://content.honeywell.com/sensing/sensotec/catpages.asp>.