AUTOMOTIVE

RoHS

COMPLIANT

HALOGEN

FREE


GREEN

(5-2008)



www.vishay.com Vishay Semiconductors

Low Current 0603 SMD LED



DESCRIPTION

The new 0603 LED series have been designed in the smallest SMD package. This innovative 0603 LED technology opens the way to


- Smaller products of higher performance
- · More design in flexibility
- Enhanced applications


The 0603 LED is an obvious solution for small-scale, high power products that are expected to work reliability in an arduous environment.

PRODUCT GROUP AND PACKAGE DATA

Product group: LED
Package: SMD 0603
Product series: low current
Angle of half intensity: ± 80°

FEATURES





- Temperature range 40 °C to + 100 °C
- Footprint compatible to 0603 chipled
- Wavelength 633 nm (red), 606 nm (orange), 587 nm (yellow)
- AllnGaP technology
- · Compatible to IR reflow soldering
- Viewing angle: Extremely wide 160°
- · Grouping parameter: Luminous intensity, wavelength
- Available in 8 mm tape
- Preconditioning according to JEDEC level 2
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Backlight keypads
- Navigation systems
- Cellular phone displays
- Displays for industrial control systems
- Automotive features
- Miniaturized color effects
- · Traffic displays

PARTS TABLE														
PART	COLOR	OR (mcd) at I _F (nm) at I _F		FORW	FORWARD VOLTAGE (V)		at I _F	TECHNOLOGY						
		MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	(IIIA)	
TLMS1000-GS08	Red	1.8	4	-	2	624	628	636	2	1	1.8	2.6	2	AllnGaP
TLMO1000-GS08	Soft orange	3.55	7.5	-	2	600	605	609	2	-	1.8	2.6	2	AllnGaP
TLMY1000-GS08	Yellow	3.55	7.5	-	2	580	588	595	2	-	1.8	2.6	2	AllnGaP

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25 ^{\circ}C$, unless otherwise specified) TLMS1000, TLMO1000, TLMY1000							
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT			
Reverse voltage (1)		V_{R}	12	V			
DC Forward current	T _{amb} ≤ 95 °C	I _F	15	mA			
Surge forward current	t _p ≤ 10 μs	I _{FSM}	0.1	Α			
Power dissipation		P _V	40	mW			
Junction temperature		Tj	120	°C			
Operating temperature range		T _{amb}	- 40 to + 100	°C			
Storage temperature range		T _{stg}	- 40 to + 100	°C			
Soldering temperature	acc. Vishay spec	T _{sd}	260	°C			
Thermal resistance junction/ambient	mounted on PC board (pad size > 5 mm ²)	R _{thJA}	500	K/W			

Note

(1) Driving the LED in reverse direction is suitable for short term application

TLMO1000, TLMS1000, TLMY1000

Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified) TLMS1000, RED						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity	I _F = 2 mA	I _V	1.8	4	-	mcd
Dominant wavelength	I _F = 2 mA	λ_{d}	624	628	636	nm
Peak wavelength	I _F = 2 mA	λ_{p}	-	640	-	nm
Angle of half intensity	I _F = 2 mA	φ	-	± 80	-	deg
Forward voltage	I _F = 2 mA	V _F	-	1.8	2.6	V
Reverse voltage	I _R = 10 μA	V _R	6	=	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	15	-	pF

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 ^{\circ}$ C, unless otherwise specified) TLMO1000, SOFT ORANGE						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity	I _F = 2 mA	I _V	3.55	7.5	-	mcd
Dominant wavelength	I _F = 2 mA	λ_{d}	600	605	609	nm
Peak wavelength	I _F = 2 mA	λρ	-	610	-	nm
Angle of half intensity	I _F = 2 mA	φ	-	± 80	-	deg
Forward voltage	I _F = 2 mA	V_{F}	-	1.8	2.6	V
Reverse voltage	I _R = 10 μA	V _R	6	-	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	C _j	-	15	-	pF

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified) TLMY1000, YELLOW							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity	I _F = 2 mA	I _V	3.55	7.5	-	mcd	
Dominant wavelength	I _F = 2 mA	λ_{d}	580	588	595	nm	
Peak wavelength	I _F = 2 mA	λρ	-	591	-	nm	
Angle of half intensity	I _F = 2 mA	φ	-	± 80	-	deg	
Forward voltage	I _F = 2 mA	V _F	-	1.8	2.6	V	
Reverse voltage	I _R = 10 μA	V _R	6	-	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	15	-	pF	

COLOR CLASSIFICATION							
	DOMINANT WAVELENGTH (nm)						
GROUP	YELL	LOW	ORANGE				
	MIN.	MAX.	MIN.	MAX.			
2	580	583	600	603			
3	583	586	602	605			
4	586	589	604	607			
5	589	592	606	609			
6	592	595					

Note

• Wavelengths are tested at a current pulse duration of 25 ms and an accuracy of \pm 1 nm

LUMINOUS INTENSITY CLASSIFICATION						
GROUP	LUMINOUS INTENSITY (mcd)					
GROUP	MIN.	MAX.				
G1	1.80	2.24				
G2	2.24	2.80				
H1	2.80	3.55				
H2	3.55	4.50				
J1	4.50	5.60				
J2	5.60	7.10				
K1	7.10	9.00				
K2	9.00	11.20				
L1	11.20	14.00				
L2	14.00	18.00				

Note

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Relative Luminous Intensity vs. Forward Current




Fig. 3 - Dominant Wavelength vs. Forward Current




Fig. 2 - Forward Current vs. Forward Voltage




Fig. 4 - Change of Dominant Wavelength vs. Ambient Temperature

[•] Luminous intensity is tested at a current pulse duration of 25 ms and an accuracy of ± 11 %.

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each reel (there will be no mixing of two groups on each reel).

In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped in any one reel. In order to ensure availability, single wavelength groups will not be orderable.




Fig. 5 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 6 - Forward Voltage vs. Ambient Temperature




Fig. 7 - Relative Luminous Intensity vs. Forward Current




Fig. 8 - Forward Current vs. Forward Voltage




Fig. 9 - Dominant Wavelength vs. Forward Current




Fig. 10 - Change of Dominant Wavelength vs.
Ambient Temperature




Fig. 11 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 12 - Forward Voltage vs. Ambient Temperature




Fig. 13 - Relative Luminous Intensity vs. Forward Current




Fig. 14 - Forward Current vs. Forward Voltage




Fig. 15 - Dominant Wavelength vs. Forward Current




Fig. 16 - Change of Dominant Wavelength vs.
Ambient Temperature

ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Fig. 17 - Relative Luminous Intensity vs. Ambient Temperature





Fig. 18 - Forward Voltage vs. Ambient Temperature

REEL DIMENSIONS in millimeters



Drawing-No.: 9.800-5086.01-4

Issue: 1; 29.04.04


19043

Not indicated tolerances ±0.05 Material: black static dissipative

Rev. 1.9, 09-Jul-13 6 Document Number: 83172



TAPE DIMENSIONS in millimeters




Drawing-No.: 9.700-5290.01-4

Issue: 2; 10.07.06


19044

PACKAGE DIMENSIONS in millimeters



Not indicated tolerances ±0.1

Recommended solder pad




Drawing-No.: 6.541-5056.01-4

Issue: 2; 04.05.05


19426

SOLDERING PROFILE



DRY PACKING

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.





TLMO1000, TLMS1000, TLMY1000

Vishay Semiconductors

FINAL PACKING

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 1 year under these conditions moisture content will be too high for reflow soldering.


In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

192 h at 40 °C + 5 °C/- 0 °C and < 5 % RH (dry air/nitrogen) or

96 h at 60 °C + 5 °C and < 5 % RH for all device containers or

24 h at 100 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC standard JESD22-A112 level 2 label is included on all dry bags.



Example of JESD22-A112 level 2 label

ESD PRECAUTION

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electro-static sensitive devices warning labels are on the packaging.

VISHAY SEMICONDUCTORS STANDARD BAR CODE LABEL

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000