High Accuracy Heavy-Duty Pressure Transducers





FEATURES

- Advanced diffused semiconductor and sputtered thin film sensor for maximum stability
- High accuracy and long term
 stability
- Ranges from vacuum to 145,000 psi
- Corrosion resistant stainless steel construction
- Span and zero adjustments
- Compatible with NOSHOK 1800, 1900 and 2000 Series Smart System Indicators

APPLICATIONS

- Hydraulic and pneumatic systems
- Industrial machinery and machine tools
- Injection molding machines
- Stamping and forming presses
- Pumps and compressors
- Laboratory and test equipment
- Railroad equipment
- HVAC systems
- Medical
- Refrigeration equipment
- Marine
- Power generation
- Construction
- Petrochemical
- Water management



Also available with our 1800 Series Attachable Loop Indicator. See page 44 for more information.

615/616 SERIES

- Designed for heavy-duty applications requiring high accuracy and durability
- Extreme high pressure ranges from vacuum to 145,000 psi; Absolute ranges from 15 psia to 300 psia
- · Span and zero adjustments
- Advanced diffused semi-conductor and sputtered thin film sensor for maximum stability
- Excellent accuracy, shock resistance, and long term reliability

- Rugged corrosion-resistant stainless steel construction
- Available in a wide variety of electrical and process configurations
- Compatible with NOSHOK 1900C and 2000 Series Smart System Indicators
- Also available with our 1800 Series Attachable Loop Indicator
- · CE compliant to suppress RFI, EMI and ESD
- Final calibration tests prior to shipment ensures 100% "out of the box" reliability

	SPECIFICATIONS					
Output signals	4 mA to 20 mA, 2-wire; 1 Vdc to 5 Vdc, 1 Vdc to 6 Vdc, 1 Vdc to 11 Vdc, 3-wire; 0 Vdc to 5 Vdc and 0 Vdc to 10 Vdc, 3-wire; 0 Vdc to 5 Vdc and 0 Vdc to 10 Vdc, 4-wire					
Pressure ranges	Standard gauge ranges from vacuum to 145,000 psig; Standard absolute ranges from 15 psia to 300 psia					
Proof pressure	3 times full scale for ranges 0 psi to 2 psi through 0 psi to 200 psi 1.75 times full scale for ranges 0 psi to 300 psi through 0 psi to 10,000 psi 1.5 times full scale for 0 psi to 15,000 psi range 1.2 times full scale for ranges 0 psi to 20,000 psi through 0 psi to 145,000 psi					
Burst pressure	3.8 times full scale for ranges 0 psi to 2 psi through 0 psi to 200 psi 4 times full scale for ranges 0 psi to 300 psi through 0 psi to 10,000 psi 3 times full scale for 0 psi to 15,000 psi range 1.5 times full scale for ranges 0 psi to 20,000 psi through 0 psi to 145,000 psi					
Accuracy	\pm 0.25% full scale (BFSL); optional \pm 0.125% full scale (BFSL); (includes the effects of non-linearity, hysteresis, non-repeatability, zero point and full scale errors)					
Repeatability	≤ ±0.05% full scale					
Hysteresis	≤ ±0.1% full scale					
Stability	≤ ±0.2% full scale for 1 year, non-accumulating					
Power supply*	10 Vdc to 30 Vdc (4 mA to 20 mA, 2-wire) 10 Vdc to 30 Vdc (1 Vdc to 5 Vdc, 3-wire) 10 Vdc to 30 Vdc (1 Vdc to 6 Vdc, 3-wire) 10 Vdc to 30 Vdc (0 Vdc to 5 Vdc, 3-wire) 14 Vdc to 30 Vdc (0 Vdc to 10 Vdc, 3-wire) 14 Vdc to 30 Vdc (1 Vdc to 11 Vdc, 3-wire) 14 Vdc to 30 Vdc (1 Vdc to 11 Vdc, 3-wire)					
Load limitations	≤ (VPower-10)/0.020 Amp for 4 mA to 20 mA ≥ 10,000 Ω for 0 Vdc to 10 Vdc, 3-wire ≥ 5,000 Ω for 0 Vdc to 5 Vdc, 3-wire					
Wetted materials	316 stainless steel for vacuum through 300 psi; 17-4PH stainless steel sensing diaphragm and 316 stainless steel process connection for higher ranges					
Housing materials	316 stainless steel					
Temperature ranges	Compensated 32 °F to 175 °F (0 °C to 80 °C) Effect \pm 0.01%/ °F for zero and span Storage - 40 °F to 212 °F (-40 °C to 100 °C) Medium - 20 °F to 212 °F (-30 °C to 100 °C) Ambient - 15 °F to 175 °F (-10 °C to 80 °C)					
Response time	Less than 1 ms (between 10% and 90% full scale)					
Durability	>100,000,000 full scale cycles					
Adjustment	± 10% full scale for zero and span					
Environmental protection	ction NEMA 4X, IP65 (IEC 529)					
Electromagnetic rating	2004/108/EEC, EN 61326 Emission (Group 1, Class B) and Immunity (industrial locations)					
Electrical protection	Reverse polarity, overvoltage and short circuit protection					
Shock	Less than $\pm0.05\%$ full scale effect or 1,000 g's @ 20 ms on any axis					
Vibration	Less than ± 0.01% full scale effect for 15 g's @ 0 Hz to 2,000 Hz on any axis					
Weight	Approximately 7.2 oz.					


^{*} Unregulated power supplies

WIRING DIAGRAMS ELECTRICAL CONNECTIONS

						0	DEDING INFOR	AATION					
							RDERING INFORM						
SERIES 615 (Internal diaphragm)			616	(Front flush diaphra	agm)								
PRESSURE RANGES		30vac	-30 inHg to 0 psig	2	0 psig to 2 psig	150	0 psig to 150 psig	2000	0 psig to 2,000 psig	20000	0 psig to 20,000 psig	145000	0 psig to 145,000 psig
		30/15	-30 inHg to 15 psig	3	0 psig to 3 psig	200	0 psig to 200 psig	3000	0 psig to 3,000 psig	30000	0 psig to 30,000 psig	15A	0 psia to 15 psia
		30/30	-30 inHg to 30 psig	5	0 psig to 5 psig	300	0 psig to 300 psig	4000	0 psig to 4,000 psig	36000	0 psig to 36,000 psig	30A	0 psia to 30 psia
		30/60	-30 inHg to 60 psig	10	0 psig to 10 psig	500	0 psig to 500 psig	5000	0 psig to 5,000 psig	58000	0 psig to 58,000 psig	60A	0 psia to 60 psia
		30/100	-30 inHg to 100 psig	15	0 psig to 15 psig	600	0 psig to 600 psig	6000	0 psig to 6,000 psig	72000	0 psig to 72,000 psig	100A	0 psia to 100 psia
		30/150	-30 inHg to 150 psig	30	0 psig to 30 psig	750	0 psig to 750 psig	7500	0 psig to 7,500 psig	87000	0 psig to 87,000 psig	150A	0 psia to 150 psia
		30/200	-30 inHg to 200 psig	60	0 psig to 60 psig	1000	0 psig to 1,000 psig	10000	0 psig to 10,000 psig	100000	0 psig to 100,000 psig	200A	0 psia to 200 psia
		30/300	-30 inHg to 300 psig	100	0 psig to 100 psig	1500	0 psig to 1,500 psig	15000	0 psig to 15,000 psig	115000	0 psig to 115,000 psig	300A	0 psia to 300 psia
		psig =	gauge pressure p	sia = a	bsolute pressure	Othe	r ranges available on	special re	quest Note: Series	s 616 is no	t available in pressure ra	anges 10,	000 psig and above
ACCURACIES 1 ±0.25% full scale (BFSL)			2 ±0.125% full scale (BFSL)										
OUTPUT SIGNA	LS	1	4 mA to 20 mA, 2-wire 2 0 Vdc to 5 Vdc, 3-wire 3 1 Vdc to 5 Vdc, 3-wire			4	4 1 Vdc to 6 Vdc, 3-wire*						
*Ranges up to 0	psig	2				5	0 Vdc to 10 Vdc, 3-	wire	NOTE: 0 Vdc to 5 Vdc and 0 Vdc to 10 Vdc outputs are also available in 4-wire			ilable in 4-wire	
to 60,000 psig		3				6	1 Vdc to 11 Vdc, 3-	wire*	configurations for use with other electrical systems.				
			1/4" NPT Male			9/16"-18 UNF 2B h	igh pres	sure cone*		4/ONNET M. I			
PROCESS	615:	2				6		d on 30,000 to 120,000 psig)		8	1/2" NPT Male		
CONNECTIONS	616:	11	G 1/2 B (Pressure rar	naes ≤	0 psia to 30 psia)	13	G 1 B (Pressure rai	naes≤0	psia to 30 psia)		Other connections av	ailable ur	oon request
ELECTRICAL		1	36" cable (connected to option 8)			8	,		1 0 1 07	25	M12 x 1 (4-pin)		
CONNECTIONS		3	6-pin Bendix			14	Hirschmann type w		,	36	Integral 36" cable		
			5 1/2" NPT conduit w/ 36" cable								3		
OPTIONS		ORF	SS Threaded orifice		· ·	G1	G 1 Weld-on adapt	er (616 o	nlv)	G½	G 1/2 Weld-on adapte	er (616 or	ılv)
								1	77			1	*/

^{*} Equivalent to F250C Parker Autoclave

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.



2-WIRE WIRING

	Hirschmann	Cable	M12	Bendix
+ Supply	1	Red	1	Α
+ Output	2	Black	3	В

	Hirschmann	Cable	M12	Bendix
+ Supply	1	Red	1	А
Common	2	Black	3	В
+ Output	3	White	4	С

NOTE
See 621/622 Series
for G1/2B and G1B
Front Flush Process
Connection Dimensions
pg. 29