


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 10 uF, +/-10% Tol, 25V@85C, Lead Spacing=2.54 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	5.5	
H	11.2	
F	0.5	+/-0.05
S	2.54	+/-0.38
LL	4.75	+/-0.81

Notes:
 -Height includes stand-off crimp

General Information	
Supplier:	KEMET

Specifications	
Value:	10 uF
Voltage DC @ 85C:	25V
Voltage DC @ 125C:	16.5V
Tolerance:	+/-10%
Body Type:	Radial Conformal (Dipped)
Temperature Range:	-55/+125C
Application:	General Purpose
Termination Type:	Tin (Sn)
RoHS:	Yes
Leakage Current:	2 uA
Dissipation Factor:	6%

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1000