


Capacitor, Tantalum, 47 uF, +/-10% Tol, 25V@85C



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	7.11	
L	13.46	
F	0.64	+/-0.05
LL	38.1	+/-6.35

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag

General Information	
Supplier:	KEMET

Specifications	
Value:	47 uF
Voltage DC @ 85C:	25V
Voltage DC @ 125C:	17V
Tolerance:	+/-10%
Application:	General Purpose
Body Type:	Axial Molded
Temperature Range:	-55/+125C
Termination Type:	Tin (Sn)
RoHS:	Yes
ESR:	1 Ohm
ESR Frequency @ 25C:	100 kHz
Leakage Current:	9.4 uA
Dissipation Factor:	6%