



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SM3000RML2UTAA

TAA Compliant SmartPro 3kVA 2.88kW Line Interactive Extended Run UPS, Sine wave, SNMP option, 2U, LCD, USB, Serial, EPO, 120V

Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 3kVA / 3000VA / 2880W line interactive 2U rack/tower UPS
- 120V nominal output during brownouts to 83V and overvoltages to 145V
- Interactive LCD provides UPS status information and advanced configuration options
- Expandable runtime, Hot-swap batteries, 96% efficiency, Sine wave output
- USB, RS232 & EPO ports, Support for SNMP/WEB card option
- NEMA L5-30P input; 8 NEMA 5-15/20R & 1 L5-30R outlets
- **This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment**



Description

Tripp Lite SmartPro Line Interactive UPS with enhanced LCD interface offers network-grade power protection for critical server, network and telecommunications equipment. Line Interactive Uninterruptible Power Supply (UPS) with built-in Auto-Voltage Regulation (AVR) actively corrects brownouts and overvoltages back to usable levels while maintaining a full battery charge in case of power failure. Tripp Lite's unique configuration excels in exceptionally poor-power environments with two separate levels of voltage boost to correct both slight undervoltages and severe brownout conditions. Interactive LCD/LED interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Super-fast switchover from line to battery power occurs within milliseconds to maintain operation of connected equipment without interruption or reboot. 96% line-mode efficiency offers reduced heat emissions and operating costs. Network management interfaces support communications via USB, RS-232 and optional SNMP/WEBCARD network interface. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Network communications ports enable detailed monitoring of equipment load levels, self-test data and utility power conditions. Includes PowerAlert monitoring software and complete cabling. Switched output load banks enable scheduled and real-time remote reboot and load shedding of select outlets. Emergency Power Off (EPO) interface. LED/LCD display panel easily rotates for viewing in rackmount or tower configurations. Audible alarm with push-button momentary alarm-cancel and silent-mode configuration options. Programmable self-test. Field-replaceable, hot-swappable battery modules.

Applications

Ideal for server, networking and telecommunications equipment

Package Includes

- SM3000RML2UTAA UPS system
- PowerAlert Software with USB, Serial & EPO cabling
- 4 post rackmount installation kit
- Instruction manual

Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Tripp Lite SM3000RML2UTAA line interactive 2U rack/tower UPS with 3000VA / 3kVA capacity and extended runtime options
- Line interactive UPS with Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages from 83 to 145V
- NEMA L5-30P input plug; 8 NEMA 5-15/20R and 1 L5-30R output receptacles, Two independently switchable output load banks
- Maintains uninterrupted operation of connected networking equipment during blackouts, surges, brownouts and overvoltages
- High 96% efficiency rating in line-power mode offers reduced power consumption and BTU emissions
- Internal batteries offer 10 minutes at 50% load (1440W) and 3 minutes at 100% load (2880W)
- Extended runtime is available with optional BP48V24-2U (limit 1) OR BP48V60RT3U (no limit) external battery packs
- External battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Hot-swappable, user-replaceable internal batteries and external battery packs can be replaced with no disruption to connected equipment

- Front panel LCD monitoring screen with MODE and ENTER buttons reports operating mode with 5-bar battery charge graphic, plus 7 selectable screens of detailed UPS and site power information
- LCD interface also supports a number of advanced user setup and operating preferences
- Ships with 4 post rackmount installation hardware; Optional 2POSTRMKITWM enables 2 post rackmount/wallmount installation; Optional 2-9USTAND enables tower placement
- Built-in USB, RS-232 and optional SNMPWEBCARD accessory monitoring options
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Included PowerAlert UPS monitoring software; Built-in Emergency Power Off (EPO) interface with cable

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output kVA capacity (kVA)	3
Output Watt Capacity (watts)	2880
Output kW capacity	2.88
Output power factor	.96
Nominal Output Voltage(s) Supported	120V
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	+6%, -14%
Output voltage regulation (Battery mode)	+/-5%
Built-in UPS output receptacles	8 5-15/20R outlet(s); 1 L5-30R outlet(s)
Built-in controllable switched load banks	Two switchable single outlet 5-15/20R load banks
Output circuit breaker	Two 20A output breakers protect 4 5-15/20R outlets each
Output AC waveform (AC mode)	Pure Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	24A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	L5-30P
UPS Input cord length (ft.)	10
UPS Input cord length (m)	3

Recommended Electrical Service	30A 120V
BATTERY	
Full load runtime (minutes)	3 min. (2880w)
Half load runtime (minutes)	10 min. (1440w)
Expandable battery runtime	Extended runtime supported via optional external battery packs
External battery pack compatibility	BP48V24-2U (limit 1); BP48V60RT-3U (multi-pack compatible)
DC system voltage (VDC)	48
Battery recharge rate (included batteries)	Less than 5 hours from 10 to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC58-2U
Battery Access	Front panel battery access door
Battery replacement description	Hot-swappable, replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage correction	Input voltages between 108 and 96 are boosted by 12%
Severe undervoltage correction	Input voltages between 83 and 95 are boosted by 24%
LEDS ALARMS & SWITCHES	
Front panel LCD display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Alarms	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
Alarm cancel operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	570
EMI / RFI AC noise suppression	Yes
AC suppression response time	Instantaneous
PHYSICAL	

Installation form factors supported with optional accessories	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND)
Primary form factor	Rackmount
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.5 x 17.5 x 19
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	8.9 x 44.4 x 48.3
Rack Height	2U
Secondary form factor	Tower (requires 2-9USTAND)
UPS / Power Module weight (lbs)	84.6
UPS / Power Module weight (kg)	38.4
UPS Shipping dimensions (height x width x depth / inches)	9 x 23.5 x 20
UPS Shipping dimensions (height x width x depth / cm)	22.9 x 59.7 x 50.8
Shipping weight (lbs)	84.6
Shipping weight (kg)	38.4
Cooling method	Fan
UPS housing material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	409
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions
PowerAlert software	Included
Communications cable	USB, DB9 and EPO cabling included

LINE / BATTERY TRANSFER	
Transfer time	5 milliseconds (AC to battery mode), 1 millisecond (Battery to AC mode)
Low voltage transfer to battery power (setpoint)	83
High voltage transfer to battery power (setpoint)	145
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); TAA Compliant; ENERGY STAR Qualified
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Related Model	Description	Qty.
BP48V242UTAA	TAA Compliant External Battery Pack for select UPS Systems	1
BP48V60RT3UTAA	TAA Compliant External Battery Pack and Cable. 3U, Expandable, Blue 2-Point Connector	1
SNMPWEBCARDTAA	TAA-Compliant SNMPWEBCARD for remote monitoring and control via SNMP, Web or telnet	1
WEXT3-2200-3000	3-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA	1
WEXT5-2200-3000	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA or less	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SR SWITCH	Magnetic Door Switch Kit (2-pack for front and rear doors; requires ENVIROSENSE.)	1
2-9U STAND	Enables Tower Placement of Rackmount UPS Systems	1
2POSTRMKITWM	Enables 2-Post Rackmount or Wallmount Installation of Select Rackmount UPS Systems	1
RBC58-2U	2U UPS Replacement Battery Cartridge for select Tripp Lite UPS systems	1
PDU2430	Single-Phase Basic PDU, 30A 120V, 1U Horizontal Rackmount, NEMA 5-15R outlets, NEMA L5-30P input plug	1

PDUB30	Single-Phase Hot-Swap PDU, 30A 120V, 2U Horizontal Rackmount, NEMA 5-15/20R & L5-30R outlets, set of 2 NEMA L5-30P input plugs	1
PDUMH30	Single-Phase Metered PDU, 30A 120V, 1U Horizontal Rackmount, NEMA 5-15/20R outlets, NEMA L5-30P input plug	1
PDUMH30AT	Single-Phase Auto Transfer Switch / Metered PDU, 30A 120V, 2U Horizontal Rackmount, 5-15/20R & L5-30R outlets, two L5-30P inputs	1
PDUMH30ATNET	Single-Phase Auto Transfer Switch / Switched PDU, 30A 120V, 2U Horizontal Rackmount, 5-15/20R & L5-30R outlets, 2 L5-30P inputs	1
PDUMH30NET	Single-Phase Switched PDU, 30A 120V, 2U Horizontal Rackmount, NEMA 5-15/20R outlets, NEMA L5-30P input plug.	1
PDUMNH30	Single-Phase Monitored PDU, 30A 120V, 2U Horizontal Rackmount, 5-15/20R outlets, L5-30P input	1
PDUMNV30	Single-Phase Monitored PDU, 30A 120V, 0U Vertical Rackmount, NEMA 5-15/20R outlets, NEMA L5-30P input plug	1
PDUMV30	Single-Phase Metered PDU, 30A 120V, 0U Vertical Rackmount, NEMA 5-15/20R outlets, NEMA L5-30P input plug	1
PDUMV30NET	Single-Phase Switched PDU, 30A 120V, 0U Vertical Rackmount, NEMA 5-15/20R outlets, NEMA L5-30P input plug	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4407.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.