



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SR25UBTAA

### TAA Compliant 25U SmartRack Premium Enclosure (includes doors and side panels)



#### Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 25U SmartRack enclosure with doors and side panels
- 4 interior vertical posts with unthreaded square hole openings
- Standard 24" (600mm) width and 42" (1050mm) depth for optimizing floor space
- Ships fully assembled
- Massive front to rear ventilation capacity
- 3000 lb stationary / 2250 lb rolling load capacity
- Locking, removable, reversible front and rear doors
- Locking, removable side panels keyed alike with doors
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) compliance

#### Description

SR25UBTAA meets the requirements of the Trade Agreements Act (TAA). TAA compliance applies to GSA Schedule and IDIQ contract purchases, and requires that products be assembled within the United States or in an approved country.

Tripp Lite's SR25UBTAA premium SmartRack Enclosure Cabinet is packed with features designed to simplify rack equipment installations and rack equipment maintenance: top and bottom cable routing ports, perforated door and side panels to promote efficient airflow, adjustable vertical mounting rails and more. And as part of the SmartRack family, the SR25UBTAA is compatible with Tripp Lite's extensive range of rackmount accessories, enabling you to customize your solution to meet any requirement. The SR25UB ships fully assembled on removable casters for quick installation (Note: the casters are intended for minor position adjustments within the final installation area only and are not designed for moving the enclosure over long distances).

The SR25UBTAA has 25U of capacity and is compatible with all standard 19-inch rack equipment. The front and rear pairs of vertical rails feature square mounting holes and are numbered by rack space for easy reference. The rails are adjustable in quarter-inch increments to accommodate equipment depths from 4 to 37 inches. Adjustment is quick and convenient: simply unscrew the rails, slide them to the desired depth and restore the screws. The rails feature square mounting holes and are capable of supporting up to 3000 lb of equipment with included installation hardware (2250-lb rolling capacity).

With a locking, reversible front door and locking, removable side panels, SR25UBTAA provides safe, secure installation for all equipment. This prevents unauthorized access to installed equipment while making it easy for authorized personnel to perform inspections, maintenance and equipment replacement. The enclosure meets all requirements toward PCI DSS compliance.

The top and bottom panels of the SR25UBTAA are furnished with vents designed to help remove warm air from the enclosure and draw in cool air by convection. They also support installation of standard user-supplied case fans (Tripp Lite SRFANROOF). The top and bottom panels are also provided with ports for cable routing.

SR25UBTAA has a 5-year product warranty.

#### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Ships fully assembled for rapid deployment and roll into place on heavy-duty pre-installed casters (casters are removable)
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring time-consuming measurements.
- Toolless accessory mounting rails (2 rails per enclosure) include slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.

- Massive front to rear ventilation capacity. 65+% open space in door perforation pattern meets or exceeds server manufacturer requirements.
- Maximum usable internal depth of 37 inches/94 cm (front to rear rail).
- Weight ratings of 3000 lb stationary and 2250 lb rolling.
- Front door is locking, reversible and removable.
- Rear doors are locking and reversible. Split rear door design reduces clearance requirements for service entry allowing the enclosure to be placed closer to a wall.
- Locking removable side panels are 'half size' to make them smaller and lighter improving ease of installation and servicing. Side panels are keyed alike to the front and rear doors.
- Built in baying tabs allow enclosures to be combined securely in rows. Center-to-center width can be set at 600mm or 24" to match standard data center floor tiles.
- Leveling feet extend to allow enclosure to be positioned on uneven floors. Levelers are removable.
- Compact shorter design for when a full height enclosure is not needed.
- Convenient grounding system. All components are grounded to the enclosure frame which includes multiple connections for facility ground. Front and rear doors include quick-release ground wires.
- Open bottom for cable access.
- Top panel has generous cable access holes. Panel can be removed toollessly in seconds without having to disconnect cables first.
- Included stabilizing brackets are used for shipment and can be reattached at the bottom of the enclosure frame on the inside or outside of the rack.
- Meets all enclosure

## Specifications

PHYSICAL	
Installed whole system maximum rack depth (inches)	37
Installed whole system maximum rack depth (cm)	94.0
Installed whole system minimum rack depth (inches)	4
Shipping Dimensions (HWD/in)	55 x 27.75 x 47
Shipping Dimensions (HWD/cm)	139.7 x 70.48 x 119.38
Shipping weight (lbs)	218
Shipping weight (kg)	98.88
Unit Dimensions (HWD/in)	EXTERNAL DIMENSIONS: 49 x 23.63 x 43
Unit Dimensions (HWD/cm)	124.46 x 60.02 x 109.22
Unit weight (lbs)	195
Unit weight (kg)	88.45
Color	Black
Style	Floor Standing
Weight Capacity - Stationary (lbs)	3000
Weight Capacity - Rolling (lbs)	2250
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">B020-U08-19-IP</a>	Console KVM Switch - 8-Port NetDirector 1U Rackmount Console IP KVM Switch w/17" LCD	1
<a href="#">B021-000-17</a>	Rackmount Console - 1U Rackmount Console with 17" LCD	1
<a href="#">B021-000-19</a>	Rackmount Console - 1U Rackmount Console with 19" LCD	1
<a href="#">B040-008-19</a>	NetController 19" VGA Console KVM Switch - 8 Port	1
<a href="#">B040-016-19</a>	NetController 19" VGA Console KVM Switch - 16 Port	1
<a href="#">N252-012</a>	12-Port Cat6 Patch Panel 568B	1
<a href="#">N252-024</a>	24-Port Cat6 Patch Panel 568B	1
<a href="#">N252-048</a>	48-Port Cat6 Patch Panel 568B	1
<a href="#">SRBOLTDOWN</a>	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	1
<a href="#">SRCABLEDUCTVRT</a>	6-ft. (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	1
<a href="#">SRCABLEDUCT1U</a>	1U Horizontal Cable Manager (Finger duct with cover.)	1
<a href="#">SRCABLELADDER</a>	10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	1
<a href="#">SRCABLERINGVRT</a>	6-ft. (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	1
<a href="#">SRCABLERING1U</a>	1U Horizontal Cable Manager (Flexible ring type.)	1
<a href="#">SRCABLERING2U</a>	2U Horizontal Cable Manager (Flexible ring type.)	1
<a href="#">SRCABLETRAY</a>	Roof-Mounted Cable Trough (Provides cable routing and power/data cable segregation.)	1
<a href="#">SRCABLETRAYEXP</a>	Roof-Mounted Cable Trough Vertical Expansion (Requires SRCABLETRAY.)	1
<a href="#">SRCAGENUTS</a>	Square Hole Hardware Kit (Includes 50 M6 screws and washers.)	1
<a href="#">SRCOMBO</a>	Door Handles with Combination Lock (2-pack for front and rear doors; includes bypass key.)	1
<a href="#">SREXTENDER</a>	Rack Enclosure Extension Frame (Increases external depth of rack enclosures to 51-in. / 1295 mm; increases maximum mounting depth to 43.75-in. / 1111 mm.)	1
<a href="#">SRFANROOF</a>	Roof-Mounted Fan Panel, 120V (6 high-performance fans; 420 CFM; 5-15P plug; toolless mounting.)	1
<a href="#">SRFAN3U</a>	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	1
<a href="#">SRSHELF2P</a>	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	1
<a href="#">SRSHELF4PHD</a>	Heavy-Duty Fixed Shelf (250 lb / 113 kg capacity; 26 in / 660 mm depth.)	1
<a href="#">SRSHELF4PKYBD</a>	Keyboard Shelf (25 lb / 11 kg capacity; 16-in. / 406 mm depth.)	1
<a href="#">SRSHELF4PSL</a>	Standard Sliding Shelf (50 lb / 22 kg capacity; 26 in/ 660 mm depth.)	1
<a href="#">SRSHELF4PSLHD</a>	Heavy-Duty Sliding Shelf (100 lb / 45 kg capacity; 26 in / 660 mm depth.)	1
<a href="#">SRSTABILIZE</a>	Anti-Tip Stabilizing Plate Kit (Provides extra stability for standalone enclosures.)	1
<a href="#">SRSWITCH</a>	Magnetic Door Switch Kit (2-pack for front and rear doors; requires ENVIROSENSE.)	1
<a href="#">SRXFANROOF</a>	Roof-Mounted Fan Panel, 230V (6 high-performance fans; 420 CFM; C14 inlet; toolless mounting.)	1
<a href="#">SRXFAN3U</a>	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	1

<a href="#">SR1UPANEL10</a>	1U Blanking Panel Kit (10 pieces; toolless mounting.)	1
<a href="#">SR1UPANEL50</a>	1U Blanking Panel Kit (50 pieces; toolless mounting.)	1
<a href="#">UPSHDEARKIT</a>	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post or 2-post racks and enclosures. )	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4409](http://www.tripplite.com/en/products/model.cfm?txtModelID=4409).

---

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.